

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0900750031

Status:

Active

Overview:

Modular Jacks and Plugs

Description:

Modular Plug, Short Body, 6/6

Documents:

3D Model

Drawing (PDF)

Product Specification PS-90075-001 (PDF)

Application Specification AS-90075-001 (PDF)


RoHS Certificate of Compliance (PDF)

Product Literature (PDF)

Agency Certification		
UL		E107635
General		
Product Family		Modular Jacks/Plugs
Series		90075
Component Type		Wire Plug
Magnetic		No
Overview		Modular Jacks and Plugs
Performance Category		3
Power over Ethernet (PoE)		N/A
Product Literature Order No		987650-8441
Product Name		RJ11
UPC		800753868694

Physical		
Boot Color		N/A
Color - Resin		Clear
Durability (mating cycles max)		500
Flammability		94V-0
Inverted / Top Latch		N/A
Jack Height		N/A
Lightpipes/LEDs		None
Material - Metal		Copper Alloy
Material - Plating Mating		Gold
Material - Plating Termination		Tin
Material - Resin		Polycarbonate
Net Weight		0.896/g
Orientation		N/A
PCB Retention		None
Packaging Type		Bag
Pitch - Mating Interface		1.02mm
Pitch - Termination Interface		1.02mm
Plating min - Mating		1.270µm
Plating min - Termination		1.270µm
Ports		1
Positions / Loaded Contacts		6/6
Surface Mount Compatible (SMC)		No
Temperature Range - Operating		-40°C to +60°C
Termination Interface: Style		N/A
Waterproof / Dustproof		No
Wire/Cable Type		Flat Oval

Electrical		
Current - Maximum per Contact		1.5A
Grounding to Panel		N/A
Shielded		No



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -ED/01/2017 (12 January 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

90075 Series

Mates With

FCC 68 Jacks...

Voltage - Maximum	125V DC
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-90075-001
Product Specification	PS-90075-001
Sales Drawing	SDA-90075

This document was generated on 03/20/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION