

Slotted, Phillips, PlusMinus/Pozidriv 6-pcs.

3201 K601

Order-No.	
38362	1
	3,5 x 100 / 4,0 x 100 / 5,5 x 125
	PH1 x 80 / PH2 x 100
	SL/PZ2 x 100
Manufactured acc. to IEC 60900:2012.	

Slotted, Pozidriv 6-pcs.

3201 ZK6

Order-No.	
36455	1
	3,5 x 100 / 4,0 x 100 / 5,5 x 125 / 6,5 x 150
	PZ1 x 80 / PZ2 x 100
Manufactured acc. to IEC 60900:2012.	

TORX® Tamper Resistant (with hole) 6-pcs.

3251 TR K6

Order-No.	
41245	1
	T10H x 100 / T15H x 100 / T20H x 100 / T25H x 125 / T30H x 125 / T40H x 150
Manufactured acc. to IEC 60900:2012.	

TORX® 6-pcs.

3251 K6

Order-No.	
36558	1
	T8 x 60 / T9 x 60
	T10 x 100 / T15 x 100 / T20 x 100 / T25 x 125
• no slim version Manufactured acc. to IEC 60900:2012.	

Screwdriver set SoftFinish® electric slimFix**Slotted, Phillips, 2-pcs. in blister pack**

SB 3201 S201

Order-No.	
36331	1
	3,5 x 100
	PH2 x 100
Manufactured acc. to IEC 60900:2012.	

Slotted, Pozidriv, 2-pcs. in blister pack

SB 3201 S202

Order-No.	
36332	1
	3,5 x 100
	PZ2 x 100
Manufactured acc. to IEC 60900:2012.	

Slotted, PlusMinus/Pozidriv, 2-pcs. in blister pack

SB 3201 S204

Order-No.	
36333	1
	3,5 x 100
	SL/PZ2 x 100
Manufactured acc. to IEC 60900:2012.	

Screwdriver set SoftFinish® electric

1000 V IEC 60900

**Slotted, Phillips 7-pcs.**

320N K7

Order-No.	
00834	1
	2,5 x 75 / 4,0 x 100 / 5,5 x 125 / 6,5 x 150
	PH1 x 80 / PH2 x 100
	Voltage tester SoftFinish® single-pole, 110-250 volts
Manufactured acc. to IEC 60900:2012.	

Slotted, Phillips 6-pcs.

320N K6

Order-No.	
00833	10
	3,0 x 100 / 4,0 x 100 / 5,5 x 125 / 6,5 x 150
	PH1 x 80 / PH2 x 100
Manufactured acc. to IEC 60900:2012.	

Slotted, Pozidriv 6-pcs.

320N ZK6 SO

Order-No.	
25477	1
	2,5 x 75 / 3,5 x 100 / 4,5 x 125 / 5,5 x 125
	PZ1 x 80 / PZ2 x 100
Manufactured acc. to IEC 60900:2012.	