



# Super-Tip Foam Swab

2306

Precisely designed, manufactured and packaged to serve a wide variety of cleaning and maintenance needs. TechSwabs are manufactured in accordance with Techspray's rigid specifications, using specialized materials to ensure low particle generation. Cotton swabs are the most economical choice for high volume usage. Foam swabs are ideal for more precision cleaning where linting needs to be avoided.



[Request More Info](#)



## Large 1/2" wide rigid foam head


All foam swabs are manufactured with 100 pores per inch reticulated polyurethane foam, which ensures excellent absorbency while minimizing contamination. Tips are affixed by heat seal to prevent tip loss, even while saturated with solvent. Flexible tips provide versatility and softer touch, while rigid heads allow for more aggressive cleaning. 2306 swab is Techspray's most popular foam swab. Good for general purpose coating and cleaning.

- Reticulated polyurethane foam
- Head thermally bonded
- High absorbency
- Low particulate count
- Rigid head for firm touch

## Product Dimensions


### 2306-50 Mini-Tip Foam Swab

50 ct  
12 units/case



### 2306-1000 Super-Tip Foam Swab

1000 ct  
1 units/case



**Techspray**  
8125 Cobb Center Drive,  
Kennesaw, GA 30152  
800-858-4043 • [www.techspray.com](http://www.techspray.com)



---

## Environmental Policy

Techspray is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

---

## Resources

Techspray products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray products in the United States, call the technical sales department at 800-858-4043, email [tsales@techspray.com](mailto:tsales@techspray.com) or visit our web site at: [www.techspray.com](http://www.techspray.com).

### North America

Techspray  
P.O. Box 949  
Amarillo, TX 79105  
800-858-4043  
Email: [tsales@techspray.com](mailto:tsales@techspray.com)

### Europe

ITW Contamination Control  
Saffierlaan 5  
2132 VZ Hoofddorp  
The Netherlands  
+31 88 1307 400  
Email: [info@itw-cc.com](mailto:info@itw-cc.com)

### Countries Outside US

Call to locate a distributor in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.

© 2017 Techspray, A Division of ITW