

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0334721201](#)  
**Status:** **Active**  
**Overview:** [MX150™ Sealed and Unsealed Connector System](#)  
**Description:** [MX150™ Sealed Female Connector, Dual Row, 12 Circuits, Polarization A, without Connector Position Assurance, Black](#)

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification AS-33611-001-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification PK-31300-903 (PDF)</a>
<a href="#">Product Specification PS-33472-000-001 (PDF)</a>	<a href="#">Packaging Specification PK-33472-001 (PDF)</a>
<a href="#">Product Specification PS-34646-001-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification AS-33472-100-001 (PDF)</a>	

**General**

Product Family	Crimp Housings
Series	<a href="#">33472</a>
Application	Power, Wire-to-Wire
Comments	No Connector Position Assurance (CPA)
More Detailed Tech Information	<a href="http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications-Partnership">http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications-Partnership</a>
Overview	<a href="#">MX150™ Sealed and Unsealed Connector System</a>
Product Name	MX150™
UPC	756054494875

**Physical**

Circuits (maximum)	12
Color - Resin	Black, Natural
Gender	Receptacle
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene Alloy
Net Weight	15.325/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +125°C


**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

**Reference - Drawing Numbers**

Application Specification	AS-33472-100-001, AS-33611-001-001
Packaging Specification	PK-31300-903, PK-33472-001
Product Specification	PS-33472-000-001, PS-34646-001-001
Sales Drawing	150-S-012-2-Z01, SD-33472-0002-001, SD-34345-001-000



Series image - Reference only

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/01/2017 (12  
January 2017)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

[33472](#) Series

**Mates With**

[33482](#) Male Dual Row Sealed Connector

**Use With**

[33012](#) MX150™ Female Terminal,  
[34345-0001](#) MX150™ Cavity Plug Sealed