

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0449150011

Status:


Active

Overview:

Modular Jacks and Plugs

Description:

Modular Plug, Category 6, Long Body, Shielded, 8/8, without Strain Relief



Series image - Reference only

Documents:

3D Model

Drawing (PDF)

Product Specification PS-44915-003-001 (PDF)

Packaging Specification PK-44915-003 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E107635
General	
Product Family	Modular Jacks/Plugs
Series	44915
Component Type	Wire Plug
Magnetic	No
Overview	Modular Jacks and Plugs
Performance Category	6
Power over Ethernet (PoE)	N/A
Product Name	RJ45
UPC	800756395555
Physical	
Color - Resin	Clear
Durability (mating cycles max)	500
Inverted / Top Latch	N/A
Jack Height	N/A
Lightpipes/LEDs	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Polycarbonate
Net Weight	2.846/g
Orientation	N/A
PCB Locator	No
PCB Retention	None
Packaging Type	Bag
Panel Mount	N/A
Pitch - Mating Interface	1.02mm
Pitch - Termination Interface	1.02mm
Ports	1
Positions / Loaded Contacts	8/8
Temperature Range - Operating	-40°C to +85°C
Termination Interface: Style	N/A
Wire/Cable Type	Round
Electrical	
Current - Maximum per Contact	1.5A
Grounding to Panel	N/A
Shielded	Yes
Voltage - Maximum	125V
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -ED/01/2017 (12 January 2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

44915 Series

Mates With

FCC 68 Jacks

Reference - Drawing Numbers

Packaging Specification	PK-44915-003
Product Specification	PS-44915-003-001
Sales Drawing	SD-44915-001

This document was generated on 04/20/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION