

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0529865079](#)
Status: **Active**
Description: 1.27mm Pitch Wire-to-Board Shielded Receptacle, Right Angle, Dual Row, with Insert Nut for Screw Locks, 50 Circuits

Documents:

3D Model	Product Specification PS-52986-016-001 (PDF)
Drawing (PDF)	Packaging Specification SPK-52986-016-001 (PDF)
Product Specification PS-52986-001-001 (PDF)	RoHS Certificate of Compliance (PDF)

General


Product Family	I/O Connectors
Series	52986
Application	Wire-to-Board
Component Type	Receptacle
Product Name	Leaf Style Contact
Type	N/A
UPC	822348207886

Physical

Circuits (Loaded)	50
Circuits (maximum)	50
Color - Resin	Black
Durability (mating cycles max)	500
Gender	Receptacle
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze, Steel
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	9532.881/mg
Number of Rows	2
Orientation	Right Angle
PC Tail Length	3.18mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Panel Mount	Yes
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	0.305µm
Plating min - Termination	1.016µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-55°C to +85°C
Termination Interface: Style	Through Hole
Waterproof / Dustproof	No
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	1.0A
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	250V AC (RMS)/DC



EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[52986](#) Series

Mates With

[54306](#) , [52316](#)

Material Info

Reference - Drawing Numbers

Packaging Specification

Product Specification

Sales Drawing

SPK-52986-016-001

PS-52986-001-001, PS-52986-016-001

SD-52986-020

This document was generated on 05/16/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION