

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0533980671

Status:


Active

Overview:

PicoBlade™ Connector System

Description:

1.25mm Pitch PicoBlade™ Header, Surface Mount, Vertical, 6 Circuits



Series image - Reference only

Documents:

3D Model

Drawing (PDF)

Product Specification PS-51021-024-001 (PDF)

Packaging Specification SPK-53398-002-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179
General	
Product Family	PCB Headers
Series	53398
Application	Signal, Wire-to-Board
Current Derating Order No	987651-3691
MolexKits	Yes
Overview	PicoBlade™ Connector System
Product Name	PicoBlade™
UPC	822348164332
Physical	
Breakaway	No
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Compliant	No
Guide to Mating Part	No
Lock to Mating Part	Yes
Mated Height	5.70mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	214.700/mg
Number of Rows	1
Orientation	Vertical
PC Tail Length	0.60mm
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.25mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Partial
Stackable	No
Temperature Range - Operating	-40°C to +85°C
Termination Interface: Style	Surface Mount
Electrical	
Current - Maximum per Contact	1.0A
Voltage - Maximum	125V

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per

-ED/01/2017 (12

January 2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product

environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any

non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

53398 Series

Mates With

PicoBlade™ Housing 51021

PicoBlade™ Cable Assembly 15134

Material Info

Reference - Drawing Numbers

Packaging Specification	SPK-53398-002-001
Product Specification	PS-51021-024-001
Sales Drawing	SD-53398-032, SD-53398-033

This document was generated on 05/16/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION