

Zack Marker strip, flat - ZBF 5,LGS:FORTL.ZAHLEN - 0808671

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Zack Marker strip, flat, Strip, white, labeled, Printed horizontally: Consecutive numbers 1 - 10, 11 - 20, etc. up to 491 - 500, Mounting type: Snap into flat marker groove, for terminal block width: 5 mm, Lettering field: 5.15 x 5.15 mm

The figure shows the versions ZBF 5- UNBEDRUCKT, - LGS:FORTL.ZAHLEN, - QR:FORTL.ZAHLEN, and -CUS

Why buy this product

- The ZBF zack marker strip system with flat marker groove is a marking solution for modular terminal blocks and electronics modules
- Other pitches available on request
- Labeling service: Phoenix Contact can custom-label all zack marker strip markers according to your requirements
- The multi-section marking strips are easy to fit and can be easily separated if required
- Unlabeled marking strips can be custom-labeled with a plotter or by hand



Key Commercial Data

Packing unit	10 STK
Minimum order quantity	10 STK
Weight per Piece (excluding packing)	0.520 g
Custom tariff number	49119900
Country of origin	Germany

Technical data

Dimensions

Width (a)	5 mm
-----------	------

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

General

Note	For labeling according to customer requirements, please select product 0825025
Color	white
Components	free from silicone and halogen

Zack Marker strip, flat - ZBF 5,LGS:FORTL.ZAHLEN - 0808671

Technical data

General

Flammability rating according to UL 94	V2
Material	PA
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Printing direction	Printed horizontally
Printing	Consecutive numbers 1 - 10, 11 - 20, etc. up to 491 - 500
Number of individual labels	10
Number of individual labels per row	10
Number of marker strips	10
Marking mounting type	Snap into flat marker groove

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V2

Classifications

eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137
eCl@ss 9.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761
ETIM 6.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131505

Accessories

Additional products

Zack Marker strip, flat - ZBF 5,LGS:FORTL.ZAHLEN - 0808671

Accessories

Zack Marker strip, flat - ZBF 5 CUS - 0825025



Zack Marker strip, flat, can be ordered: Strip, white, labeled according to customer specifications, Mounting type: Snap into flat marker groove, for terminal block width: 5 mm, Lettering field: 5.15 x 5.15 mm