

## Zack marker strip - ZB 5,LGS:FORTL.ZAHLEN - 1050017

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Zack marker strip, Strip, white, labeled, Printed horizontally: Consecutive numbers 1 - 10, 11 - 20, etc. up to 491 - 500, Mounting type: Snap into tall marker groove, for terminal block width: 5.2 mm, Lettering field: 5.15 x 10.5 mm

The illustration shows a combination of versions, ZB 5 UNPRINTED, ZB 5 SO/CMS, as well as ZB 5 LGS- ZB 7,5 LGS CONSEC.NOS

### Why buy this product

- Other pitches available on request
- The multi-section marking strips are easy to fit and can be easily separated if required
- Labeling service: Phoenix Contact can custom-label all zack marker strip markers according to your requirements
- The ZB zack marker strip system is a marking solution for modular terminal blocks and electronics modules with tall marker grooves
- Unlabeled marking strips can be custom-labeled with a plotter or by hand



### Key Commercial Data

Packing unit	10 STK
Minimum order quantity	10 STK
Weight per Piece (excluding packing)	1.300 g
Custom tariff number	49119900
Country of origin	Germany

### Technical data

#### Dimensions

Width (a)	5 mm
-----------	------

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

#### General

Note	For labeling according to customer requirement, please select 0824962 product
Color	white

# Zack marker strip - ZB 5,LGS:FORTL.ZAHLEN - 1050017

## Technical data

### General

Components	free from silicone and halogen
Flammability rating according to UL 94	V2
Material	PA
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
	DIN VDE 0611
Printing direction	Printed horizontally
Printing	Consecutive numbers 1 - 10, 11 - 20, etc. up to 491 - 500
Number of individual labels	10
Number of individual labels per row	10
Number of marker strips	10
Marking mounting type	Snap into tall marker groove

### Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
	DIN VDE 0611
Flammability rating according to UL 94	V2

### Classifications

#### eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137
eCl@ss 9.0	27141137

#### ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761
ETIM 6.0	EC000761

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131505

## Zack marker strip - ZB 5,LGS:FORTL.ZAHLEN - 1050017

### Accessories

#### Additional products

Zack marker strip - ZB 5 CUS - 0824962



Zack marker strip, can be ordered: Strip, white, labeled according to customer specifications, Mounting type: Snap into tall marker groove, for terminal block width: 5.2 mm, Lettering field: 5.15 x 10.5 mm