

Plastic Tip Tweezers and Tips

Specially designed for the electronics industry, these tweezers feature durable and self-aligning replacement tips, anti-magnetic stainless steel handles and are available with a variety of tip geometries and materials: they offer a significant cost savings. Excellent for handling sensitive electronic components, and ceramic and glass parts where non-metallic non-scratching is critical.

Anti-Acid/Anti-Magnetic SS (SA) - CARBON FIBER (CF)

Anti-Acid/Anti-Magnetic SS (SA) - CARBON PEEK (CP)

Anti-Acid/Anti-Magnetic SS (SA) - PVDF Plastic (SV)



00CF.SA

Tips: straight, flat edges, strong, thick. OAL: 130mm.
ESD safe



00CFR.SA - 00SVR.SA

Tips: straight, flat edges, strong, thick. OAL: 130mm
A00CF - A00SV

Replacement tip set. OAL: 40mm. ESD safe



2ABCFR.SA - 2ABCPR.SA - 2ABSVR.SA

Tips: curved, flat, round. OAL: 130mm

A2ABCF - A2ABCP - A2ABSV


Replacement tip set. OAL: 40mm. ESD safe



2ACF.SA

Tips: straight, flat, round. OAL: 130mm

ESD safe




2ACFR.SA - 2ACPR.SA - 2ASVR.SA

Tips: straight, flat, round. OAL: 130mm

A2ACF - A2ACP - A2ASV

Replacement tip set. OAL: 40mm. ESD safe




2AXCFR.SA - 2AXCPR.SA - 2AXSVR.SA

Tips: straight, flat, round. OAL: 125mm. Reverse action

A2ACF - A2ACP - A2ASV

Replacement tip set. OAL: 40mm. ESD safe



2WFCPR@.SA - 2WFSVR.SA

Tips: handling 2", fine, round, strong top fingers, stepped bottom paddle. OAL: 130mm. ESD safe

A2WFCP@ - A2WFSV Replacement tip set. OAL: 40mm




3CCF.SA

Tips: straight, sharp, pointed. OAL: 115mm

ESD safe

Plastic Tip Tweezers and Tips




3CCFR.SA

Tips: straight, sharp, pointed. OAL: 115mm

A3CF

Replacement tip set. OAL: 40mm. ESD safe



3CFR.SA - 3CPR.SA

Tips: straight, sharp, pointed. OAL: 130mm

A3CF - A3CP


Replacement tip set. OAL: 40mm. ESD safe



3XCF.SA

Tips: straight, sharp, pointed. OAL: 130mm. Reverse action

ESD safe



4WFCPR@.SA - 4WFSVR.SA

Tips: handling 4", flat round, stepped bottom paddle. OAL: 130mm

A4WFCP@ - A4WFSV


Replacement tip set. OAL: 40mm. ESD safe



5CF.SA

Tips: straight, very fine. OAL: 130mm

ESD safe



5CFR.SA - 5CPR.SA - 5SVR.SA

Tips: straight, very fine. OAL: 130mm

A5CF - A5CP - A5SV


Replacement tip set. OAL: 40mm. ESD safe



5XCF.SA

Tips: straight, very fine. OAL: 125mm. Reverse action

ESD safe



5XCFR.SA - 5XCPR.SA

Tips: straight, very fine. OAL: 125mm. Reverse action

A5CF - A5CP

Replacement tip set. OAL: 40mm. ESD safe


Plastic Tip Tweezers and Tips



7CF.SA
 Tips: curved, very fine. OAL: 130mm
 ESD safe



7CFR.SA - 7CPR.SA - 7SVR.SA
 Tips: curved, very fine. OAL: 130mm
A7CF - A7CP - A7SV
 Replacement tip set. OAL: 40mm. ESD safe



242CFR.SA - 242CPR.SA - 242SVR.SA
 Tips: straight, narrow, flat, round. OAL: 130mm
A242CF - A242CP - A242SV
 Replacement tip set. OAL: 40mm. ESD safe



246CFR.SA
 Tips: thin, angled head. OAL: 125mm
A246CF
 Replacement tip set. OAL: 40mm. ESD safe



248CF.SA
 Tips: straight, broad, flat, strong. OAL: 130mm
 ESD safe



249CF.SA
 Tips: straight, strong, thick. OAL: 130mm
 ESD safe




249CFR.SA - 249CPR.SA
 Tips: straight, strong, thick. OAL: 130mm
A249CF - A249CP
 Replacement tip set. OAL: 40mm. ESD safe



250CF.SA
 Tips: straight, grooved for handling diodes, superior finish. OAL: 130mm
 ESD safe

Plastic Tip Tweezers and Tips



259CF.SA

Tips: straight, strong, pointed. OAL: 130mm
ESD safe



259CFR.SA - 259CPR.SA - 259SVR.SA

Tips: straight, strong, pointed. OAL: 130mm


A259CF - A259CP - A259SV

Replacement tip set. OAL: 40mm. ESD safe



269CF.SA

Tips: straight, thick, flat, strong for lead straightening.
OAL: 130mm
ESD safe



KCFR

Kit of tweezers: 249CFR, A7CF, A5CF, A259CF, A2ACF
ESD safe