

# MiniStation™ SSD

## Portable Hard Drive


**BUFFALO**™

SSD-PMU3

## Small and light-weight external SSD


Buffalo's MiniStation SSD is the ideal external storage device for users seeking additional storage space and fast transfer rates in the smallest and lightest possible format. Its elegant chassis measures only 80 x 49.5 x 9.4 mm and it weighs merely 30 g. MiniStation SSD's "Read" performance can reach above 420MB/s and "Write" performance above 370MB/s.

The external SSD is equipped with a USB 3.1 port – backward compatible for USB 3.0/2.0 – and can be formatted to support both PC and Mac® ensuring you can connect to most computers and devices. Thanks to its shock resistance and software encryption the SSD-PMU3 keeps data protected when on the move. For extra convenience and easy connection the portable device comes with a 30cm-long cable.



## Features and Benefits

- Fast speed – USB 3.1 interface combined with a Solid State Drive for fast data transfer rates
- Available in capacities of 120GB, 240GB, 480GB
- Compact measurements of 80 x 49.5 x 9.4 mm
- Shock resistance protects data when on the go
- Software encryption
- Extra-long USB 3.0 cable in the box
- Bus powered – No additional power input required
- Sophisticated design with a compact body



# MiniStation™ SSD

## Portable Hard Drive



SSD-PMU3

## Specifications

Internal SSD	
SSD interface	SATA 6Gbps
Capacities	120GB, 240GB, 480GB
Number of Drives	1
NAND type	TLC
USB Interfaces	
Number of Ports	1
Standard Compliance	USB 3.1 (downward compatible with USB 3.0/2.0)
Connector Type	Type A
Data Transfer Rate	5Gbps
Other	
Supported OS	Windows® 10/8.1/7, Mac® OS X 10.12/10.11/10.10/10.9
Included Software	Disk Formatter2, SecureLock Mobile2
Dimensions	80 x 49.5 x 9.4 mm
Weight	30 g
Operating environment	Temperature: 5-35°C, Humidity: 0-85% (non-condensing)
Power supply	Bus powered
Warranty	2 years
Accessories	micro B to A cable
Colour	Black

### Product Part Numbers

SSD-PM120U3B-EU  
SSD-PM240U3B-EU  
SSD-PM480U3B-EU



## About Buffalo

Buffalo Technology is a leading global provider of award-winning storage, networking and multimedia solutions for the home and small business environments as well as for system builders and integrators. With more than three decades of networking and computer peripheral experience, Buffalo has proven its commitment to delivering innovative solutions that have put the company at the forefront of infrastructure technology.

© Buffalo Inc. 2017. BUFFALO logo, AirStation, Nfiniti, AOSS, TeraStation, LinkStation, DriveStation and MiniStation are either trademarks or registered trademarks of Melco Holdings Inc. or Buffalo Inc. Microsoft Windows and Microsoft logo are either registered trademarks or trademarks of Microsoft Corporation in United States and/or other countries. The names and logos of other companies mentioned herein belong to their respective owners. The information within this datasheet is subject to change without notice. All rights reserved. E & OE.