


Scalpels and Blades

A large selection of premium quality scalpels and blades - produced with precision and consistency, combining traditional blade making skills with the latest technology. They are used in different industries from Mold cutting and Jewellery manufacture to Printing and Artwork.


Handles **no. 3**, **5A SM** and **7 SM** fit small fitment blades (310 SM, 310A SM, 311 SM, 312 SM, 313 SM, 314 SM, 315 SM).



3
Handle only



5A SM
Handle only (acrylic handle)



7 SM
Handle only



Small fitment blades
For handles 3, 5A SM, 7 SM

Handles **no. 4** and **6A SM** fit large fitment blades (418 SM, 419 SM, 420 SM, 421 SM, 422 SM, 423 SM, 424 SM, 425 SM, 425A SM, 426 SM, 436ST SM).



4
Handle only



6A SM
Handle only (acrylic handle)




Larger fitment blades
For handles 4, 6A SM

SMOR II Trimming Knife, retractable handle

PCABS handle, easy blade fitment and removal with audible clicks to indicate the mid usage position and the rear safe position for when the knife is not in use.

SMOR-II retractable handle is supplied with two SM01 SM blades and can also be used with SM01B SM, SM02 SM, SM03 SM, SM03B SM and SM04 SM blades.



4307SMOR SM

SMOR II handle with 2x SM01 blades



Blades

For handle 4307SMOR SM

Trimaway & Retractable

Trimaway purposely designed as an economic throwaway knife (**blades are NOT interchangeable**). It has a strong nylon-based handle fitted with fixed surgical quality blades and comes complete with guard.




2331 SM

Plastic Handle with 310 SM blade



2332 SM

Plastic Handle with 310A SM blade



2333 SM

Plastic Handle with 311 SM blade



2335 SM

Plastic Handle with 315 SM blade



2338 SM

Plastic Handle with 25A blade

Retractaway 2339 SM is a sleek graphite-finish metal handle offering the added safety of a hand retractable blade mechanism. It comes with five 310A SM blades. With easy blade changing it fits and safely retracts also blades 311 SM and 315 SM.



2339 SM

Handle with 5x blades 310A SM

ACM Craft Knives and Plastic craft tool



ACM Boxed Set

The ACM Boxed Set is a comprehensive set of 13 precision ground carbon steel blades, and 3 handles. With easy blade changing, the 10 blade shapes offer cutting edge versatility all from one set. Blades and handles are available on an individual basis.

ACM tool set contains:

Handles: no. 1, no. 2, no. 5

Blades for handle no. 1: ACM7 SM, ACM10 SM, ACM11 SM (3 pcs), ACM16 SM, ACM17 SM

Blades for handle no.2 and no.5: ACM2 SM (2 pcs), ACM18 SM, ACM22 SM, ACM24 SM, ACM28 SM


Plastic craft tool

Available in impact polystyrene for light work or brass, the Craft Tool is an ideal tool for marquetry, modelling, craft, studio work and horticulture. A thumbscrew is used for blade changing and retaining.



ACMH1 SM

Scalpel Handle 1 with ACM11 SM blade



ACMH5 SM

Scalpel Handle 5 with ACM28 SM blade



1235 SM / 1231 SM

Plastic Craft Tool handle / Plastic handle with 1241 SM, 1242 SM blades



Blades

For handle no. 1



Blades

For handle no. 5



Blades

For handle no. 1235 SM/1231 SM

Industrial Trimming knives | Pro-fold

Trimming knife 4313 SM is a heavy-duty fixed-blade knife with a spring-loaded mechanism for easy opening of the handle for blade changing or safe storage. Inside the handle there is a nylon holder for spare blades and each handle is supplied with 3x No. SM92 SM blades. The trimming knife is supplied complete with a smart black holster which clips onto a belt or waistband. A full range of heavy-duty blades is available.



4313 SM

Fixed trimming knife with 3x SM92 SM blades

Robust heavy duty ABS plastic, easy grip. Secure stable and precision blade cutting, suitable for SM92 SM blade. Easy blade change. Loop holder to accommodate a spiral lanyard, belt clip or key chain.



PRO-FOLD

Trimming knife with 1x SM92 SM blade

Blade material: Carbon



Blades


For handle 4313 SM



PRO-FOLD

In closed position

Utility Blade



IND001A

Single edge steel back/spine blade. Fits KNIP126 single edge scraper handle. Material: carbon

Length: 39 mm, width: 20 mm, thickness: 0.3 mm




KNIP126 - Single edge scraper

Metal single edge scraper handle with 5x IND001A blades.

Designed to accommodate IND001A. Easy slide retractable action for blade change.

Blade Remover



5505 SM - Blade remover

Safe and easy removal of all sizes of scalpel blade from both No.3 and No.4 handles