

DT Series Standard Products

Deutsch DT Series of environmentally sealed connectors designed for wire to wire applications on engine, transmission, chassis and cab.

There are two versions identified by different colours:-

Grey - Plug with orange wedge lock, Receptacle with green wedge lock. **Black** (preferred) - With enhanced seal retention and green secondary locks.

Note: Component parts are not intermountable but in the fully assembled condition, both grey and black parts are intermateable and interchangeable thus maintaining the higher levels of sealability expected within the Construction, Off-road, Heavy Goods vehicle and Agricultural market.

Wire Sealing Range

Standard - 2.24mm - 3.68mm wire insulation diameter. **Thin wall** - 1.35mm - 3.05mm wire insulation diameter (Identified by an 'E' on the Seal/End Cap).

Part Nos. - Plugs	Standard					With End Cap								
	No. of Ways	Basic Part No.	Grey Std.	Grey Thin wall	Orange Wedge	Black Std.	Black Thin wall	Green Wedge	Grey Std.	Grey Thin wall	Orange Wedge	Black Std.	Black Thin wall	Green Wedge
	2	DT06-2S	-P004	-C015	W2S	-P012	-CE06	W2S-P012	-EP04	-CE01	W2S	-EP06	-CE05	W2S-P012
	3	DT06-3S	-P004	-C015	W3S	-P012	-CE06	W3S-P012	-EP04	-CE01	W3S	-EP06	-CE05	W3S-P012
	4	DT06-4S	-P004	-C015	W4S	-P012	-CE06	W4S-P012	-EP04	-CE01	W4S	-EP06	-CE05	W4S-P012
	6	DT06-6S	-P004	-C015	W6S	-P012	-CE06	W6S-P012	-EP04	-CE01	W6S	-EP06	-CE05	W6S-P012
	8	DT06-8SA*	-P004	-C015	W8S	-EP07	-CE10	W8S-P012	-EP04	-CE01	W8S	-EP08	-CE11	W8S-P012
	12	DT06-12SA*	-P004	-C015	W12S	-EP07	-CE10	W12S-P012	-EP04	-CE01	W12S	-EP08	-CE11	W12S-P012

*Available with B, C & D Keyways in Black, Green & Brown respectively.



Part Nos. - Receptacles	Standard					With End Cap					
	No. of Ways	Basic Part No.	Grey Std.	Grey Thin wall	Black Std.	Black Thin wall	Grey Std.	Grey Thin wall	Black Std.	Black Thin wall	Green Wedge
	2	DT04-2P	-P004	-C015	-E004	-CE02	-EP04	-CE01	-E005	-CE03	W2P
	3	DT04-3P	-P004	-C015	-E004	-CE02	-EP04	-CE01	-E005	-CE03	W3P
	4	DT04-4P	-P004	-C015	-E004	-CE02	-EP04	-CE01	-E005	-CE03	W4P
	6	DT04-6P	-P004	-C015	-E004	-CE02	-EP04	-CE01	-E005	-CE03	W6P
	8	DT04-8PA*	-P004	-C015	-E004	-CE02	-EP04	-CE01	-E005	-CE03	W8P
	12	DT04-12PA*	-P004	-C015	-E004	-CE02	-EP04	-CE01	-E005	-CE03	W12P

*Available with B, C & D Keyways in Black, Green & Brown respectively.

