

Burglar Stopper® Wire-Free Home Protection System



STI-WS100SG2

PRODUCT OVERVIEW

The Wire-Free Home Protection System, with high quality security and user-friendly features, secures your home or office. The system is controlled by a Smart Panel which receives information from wireless sensors placed in various locations throughout your home. If the Smart Panel detects a security breach, the indicator lights and audible alarms are triggered.

HOW IT WORKS

Door/Window Sensor (STI-WS102)

Panel alerts when sensor detects a protected door or window is opened. It protects access points around the home including those on or in garages, liquor cabinets, medicine cabinets, sheds, attics, side doors and freezers. Magnetic sensor can be mounted on right or left side of door or window.

PIR Motion Sensor (STI-WS103)

Motion sensor protects areas around the home. Any number of sensors can be added and it is ideal for a wide range of areas including rooms, hallways, stairwells, sheds, front and back doors. Has a 120° wide-angle detection zone and includes an all-directional mounting bracket.

Garage Door Sensor (STI-WS105)

Smart panel alerts when the sensor detects an "up-and-over" garage door is opened, sending a signal to the smart panel. It protects access points around the property and is ideal for use on raised/lowered style doors.

Inactivity Sensor (STI-WS107)

Panel alerts when sensor detects no activity is occurring in a property. Ideal for the older or more vulnerable person living independently. Selection of 12 or 24 hours.

Outdoor Bell Box (STI-WS109)

Unit has a super bright strobe light and a powerful 120 dB siren when activated by the Wire-Free Home Alarm. Ideal placement for the box is outside in a highly visible location at the front or rear of the protected property to deter intruders.

Auto Dialer/Distress Alarm (STI-WS110)

When activated, with the supplied panic remote control key fob, the auto dialer calls family, friends, colleagues or emergency services with a pre-recorded message. It can call up to eight pre-programmed telephone numbers, with a priority option and programmable dialing cycles, to assure your emergency contacts are alerted.

FEATURES

- Quick and easy installation, eliminating the mess and expense of running wires.
- Has eight pre-set security zones and four operation modes - Alarm, Alert, Home and Standby.
- Can be controlled from Smart Panel or key fob remote control (included).
- Up to 490 feet line-of-sight range.
- Adjustable entry/exit delay between 10 to 60 seconds (Arm mode only).
- Adjustable alarm duration between 1 to 6 minutes (Arm mode only).
- Back-up battery & low battery notification.
- Full back-up power supply.
- Loud 120 dB+ siren.

Burglar Stopper® Wire-Free Home Protection System

Dimensions and Technical Information

MODEL AVAILABLE

STI-WS100SG2 Burglar Stopper Wire-Free Home Protection System

System Includes:

- (1) Smart Panel
- (2) Door/Window Sensors
- (1) PIR Motion Sensor
- (1) Key Fob Remote Control

WARRANTY

One year limited warranty.

Accessories:

STI-WS102 Additional Door/Window Sensor

STI-WS103 Additional PIR Motion Sensor

STI-WS105 Garage Door Sensor

STI-WS107 Inactivity Sensor

STI-WS109 Outdoor Bell Box

STI-WS110 Auto Dialer/Distress Alarm – includes one remote (STI-WS110TX)

STI-WS101TX Additional Key Fob Remote Control

STI-WS110TX Auto Dialer Panic Remote – includes STI-WS110



STI-WS102



STI-WS103
STI-WS107



STI-WS109



STI-WS110TX



STI-WS101TX



STI-WS105



STI-WS110



**Safety Technology
International, Inc.**

2306 Airport Road
Waterford, Michigan
48327, USA

Tel: 248-673-9898
Fax: 248-673-1246
Tollfree: 800-888-4784
info@sti-usa.com
www.sti-usa.com

Unit 49G Pipers Road
Park Farm Industrial Estate
Redditch, Worcestershire
B98 0HU England

Tel: 44 (0) 1527 520 999
Fax: 44 (0) 1527 501 999
Free: 0800 085 1678 (UK)
www.sti-europe.com