



SAFETY DATA SHEET

EVO-STIK RESIN W WEATHERPROOF EXTERIOR WOOD ADHESIVE

According to Regulation (EC) No 1907/2006

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product name EVO-STIK RESIN W WEATHERPROOF EXTERIOR WOOD ADHESIVE
 Product No. 716063, 717015, 717411, 718210, 718418, 718432, 717916, 717015Sx, 717411Sx, 717916Sx, 716063Ax, S717916, S717411

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Adhesive.

1.3. Details of the supplier of the safety data sheet

Supplier BOSTIK LIMITED
 COMMON ROAD
 STAFFORD
 STAFFORDSHIRE
 ST16 3EH
 +44 1785 272625
 sds.uk@bostik.com

1.4. Emergency telephone number

+44 1785 272650 (24 Hours)

SECTION 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Physical and Chemical Hazards	Not classified.
Human health	Not classified.
Environment	Not classified.

Classification (1999/45/EEC)

Not classified.

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

2.2. Label elements

Label In Accordance With (EC) No. 1272/2008

No pictogram required.

Precautionary Statements

P102	Keep out of reach of children.
P281	Use personal protective equipment as required.

2.3. Other hazards

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

3.2. Mixtures

EVO-STIK RESIN W WEATHERPROOF EXTERIOR WOOD ADHESIVE

ALUMINIUM CHLORIDE, BASIC		1-5%
CAS-No.: 1327-41-9	EC No.: 215-477-2	
Classification (EC 1272/2008) Eye Dam. 1 - H318	Classification (67/548/EEC) Xi;R41.	

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

Composition Comments

No classified ingredients, or those having occupational exposure limits, present above the levels of disclosure.

SECTION 4: FIRST AID MEASURES

4.1. Description of first aid measures

Inhalation

Move the exposed person to fresh air at once. Get medical attention if any discomfort continues.

Ingestion

DO NOT induce vomiting. Get medical attention immediately.

Skin contact

Remove affected person from source of contamination. Rinse the skin immediately with lots of water. Get medical attention if irritation persists after washing.

Eye contact

Rinse the eye with water immediately. Continue to rinse for at least 15 minutes and get medical attention.

4.2. Most important symptoms and effects, both acute and delayed

Inhalation

No specific symptoms noted.

Ingestion

No specific symptoms noted.

Skin contact

No specific symptoms noted.

Eye contact

No specific symptoms noted.

4.3. Indication of any immediate medical attention and special treatment needed

No specific first aid measures noted.

SECTION 5: FIREFIGHTING MEASURES

5.1. Extinguishing media

Extinguishing media

This product is not flammable. Use fire-extinguishing media appropriate for surrounding materials.

5.2. Special hazards arising from the substance or mixture

Specific hazards

Fire or high temperatures create: Toxic gases/vapours/fumes of: Carbon dioxide (CO₂). Carbon monoxide (CO).

5.3. Advice for firefighters

Protective equipment for fire-fighters

Use protective equipment appropriate for surrounding materials.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Wear protective clothing as described in Section 8 of this safety data sheet.

6.2. Environmental precautions

Do not discharge into drains, water courses or onto the ground.

EVO-STIK RESIN W WEATHERPROOF EXTERIOR WOOD ADHESIVE

6.3. Methods and material for containment and cleaning up

Stop leak if possible without risk. Do not contaminate water sources or sewer. Pick up with vacuum or absorbent solid, store in closed container for disposal. Avoid generation and spreading of dust. Wear necessary protective equipment. Containers with collected spillage must be properly labelled with correct contents and hazard symbol.

6.4. Reference to other sections

Wear protective clothing as described in Section 8 of this safety data sheet.

SECTION 7: HANDLING AND STORAGE

7.1. Precautions for safe handling

Do not handle broken packages without protective equipment. Use mechanical ventilation in case of handling which causes formation of dust. Avoid spilling, skin and eye contact.

7.2. Conditions for safe storage, including any incompatibilities

Store in tightly closed original container in a dry, cool and well-ventilated place. Keep in original container.

7.3. Specific end use(s)

The identified uses for this product are detailed in Section 1.2.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

Ingredient Comments

WEL = Workplace Exposure Limits

8.2. Exposure controls

Protective equipment



Engineering measures

All handling to take place in well-ventilated area.

Hand protection

Use suitable protective gloves if risk of skin contact. Use thin cotton gloves inside the rubber gloves if allergy risk.

Eye protection

If risk of splashing, wear safety goggles or face shield.

Hygiene measures

Wash promptly if skin becomes wet or contaminated. Promptly remove any clothing that becomes contaminated. When using do not eat, drink or smoke. Wash hands at the end of each work shift and before eating, smoking and using the toilet. Use appropriate skin cream to prevent drying of skin. DO NOT SMOKE IN WORK AREA!

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

Appearance	Liquid
Colour	White.
Solubility	Miscible with water
Relative density	1.0 @ 25 °C
Flash point (°C)	N/A

9.2. Other information

SECTION 10: STABILITY AND REACTIVITY

EVO-STIK RESIN W WEATHERPROOF EXTERIOR WOOD ADHESIVE

10.1. Reactivity

No specific reactivity hazards associated with this product.

10.2. Chemical stability

Stable under normal temperature conditions.

10.3. Possibility of hazardous reactions

Not available.

10.4. Conditions to avoid

Avoid freezing conditions.

10.5. Incompatible materials

Materials To Avoid

No incompatible groups noted.

10.6. Hazardous decomposition products

Fire creates: Carbon monoxide (CO). Carbon dioxide (CO₂).

SECTION 11: TOXICOLOGICAL INFORMATION

11.1. Information on toxicological effects

Ingestion

May cause discomfort if swallowed.

Skin contact

May cause skin irritation/eczema.

Eye contact

Contact with the eyes may cause physical damage

SECTION 12: ECOLOGICAL INFORMATION

Ecotoxicity

The product components are not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

12.1. Toxicity

No data available

12.2. Persistence and degradability

Degradability

There are no data on the degradability of this product.

12.3. Bioaccumulative potential

Bioaccumulative potential

No data available on bioaccumulation.

12.4. Mobility in soil

Mobility:

Semi-mobile.

12.5. Results of PBT and vPvB assessment

No data available

12.6. Other adverse effects

Not available.

SECTION 13: DISPOSAL CONSIDERATIONS

EVO-STIK RESIN W WEATHERPROOF EXTERIOR WOOD ADHESIVE

General information

When handling waste, consideration should be made to the safety precautions applying to handling of the product.

13.1. Waste treatment methods

Dispose of waste and residues in accordance with local authority requirements. Recover and reclaim or recycle, if practical.

SECTION 14: TRANSPORT INFORMATION

General	The product is not covered by international regulation on the transport of dangerous goods (IMDG, IATA, ADR/RID).
---------	---

14.1. UN number

Not applicable.

14.2. UN proper shipping name

Not applicable.

14.3. Transport hazard class(es)

Transport Labels

No transport warning sign required.

14.4. Packing group

Not applicable.

14.5. Environmental hazards

Environmentally Hazardous Substance/Marine Pollutant

No.

14.6. Special precautions for user

Not applicable.

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.

SECTION 15: REGULATORY INFORMATION

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Statutory Instruments

The Chemicals (Hazard Information and Packaging for Supply) Regulations 2009 (S.I 2009 No. 716).

Approved Code Of Practice

Classification and Labelling of Substances and Preparations Dangerous for Supply.

Guidance Notes

Workplace Exposure Limits EH40. Introduction to Local Exhaust Ventilation HS(G)37.

EU Legislation

Dangerous Substance Directive 67/548/EEC. Dangerous Preparations Directive 1999/45/EC. Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006 with amendments.

15.2. Chemical Safety Assessment

SECTION 16: OTHER INFORMATION

General information

This product should be used as directed by Bostik Ltd. For further information consult the product data sheet or contact Technical Services.

Information Sources

This safety data sheet was compiled using current safety information supplied by distributor of raw materials.

EVO-STIK RESIN W WEATHERPROOF EXTERIOR WOOD ADHESIVE

Revision Comments

NOTE: Lines within the margin indicate significant changes from the previous revision. This safety data sheet supersedes all previous issues and users are cautioned to ensure that it is current. Destroy all previous data sheets and if in doubt contact Bostik Limited.

Issued By Approved LJ

Revision Date January 2014

Revision 10

Date February 2003

Risk Phrases In Full

NC Not classified.

R41 Risk of serious damage to eyes.

Hazard Statements In Full

H318 Causes serious eye damage.