

# ZCE06

limit switch head ZCE - cat's whisker with nitrile boot



## Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCE
Head type	Multi-directional head
Product compatibility	XCKD XCKP XCMD XCKT
Associated body	ZCMD21L08U78 ZCT25G11 ZCMD37L5 ZCT28G11 ZCP21 ZCD21 ZCMD39L5 ZCT27P16 ZCD29M12 ZCMD25L1 ZCMD29L1 ZCMD81L1 ZCD29 ZCT21G11 ZCMD61C12 ZCMD21L1 ZCP26 ZCP29 ZCP28 ZCMD41L1 ZCT28P16 ZCP25 ZCMD21L08R12 ZCD37 ZCMD69C12 ZCD21M12 ZCMD29C12 ZCD31

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

ZCD35  
 ZCMD61M12  
 ZCP31  
 ZCD25  
 ZCMD81L5  
 ZCD26  
 ZCP37  
 ZCT26P16  
 ZCT27G11  
 ZCT27N12  
 ZCD28  
 ZCMD37L1  
 ZCT21N12  
 ZCP29M12  
 ZCMD37L2  
 ZCMD39L1  
 ZCMD21L2  
 ZCP39  
 ZCD39  
 ZCT26G11  
 ZCMD25L5  
 ZCMD81L2  
 ZCMD29L5  
 ZCT28N12  
 ZCMD41L5  
 ZCD27  
 ZCT25N12  
 ZCT25P16  
 ZCMD39L2  
 ZCT26N12  
 ZCMD29L2  
 ZCP35  
 ZCP21M12  
 ZCP27  
 ZCMD41L2  
 ZCT21P16  
 ZCMD21C12  
 ZCMD21M12  
 ZCMD25L2  
 ZCMD21L5

Movement of operating head	Multi-directional
Type of operator	Cat""S whisker spring return metal (with nitrile boot)
Type of approach	Multi-directional approach

### Complementary

Switch actuation	By any moving part
Positive opening	Without

### Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0851 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------