

AX101458 Faceplates and Panels - FLEX Patch Panel - MDVO



For more Information
please call

1-800-Belden1

**General Description:**

Flex Patch Panel, 48-port, 2U, Black (Empty)

Usage (Overall)

Suitable Applications:	- Compatible with a variety of modules that are suitable for use with Belden IBDN Systems 10GX, 4800, 3600, 2400 and 1200.
Related Parts:	- Compatible with 10GX, CAT6+ and CAT5E MDVO Modular Jacks

Physical Characteristics (Connectivity)**Capacity**

Max. Capacity:	48 connectors
-----------------------	---------------

Access

Front Connection:	Flush
Termination Area:	Rear

Dimensions

Dimensions:

Height (in.)	Width (in.)	Depth (in.)
3.440	19.000	4.000

Materials

Materials:

Description	Material
Panel	Steel
Bezel	Plastic - UL94V-0

Color

Color:	Black
---------------	-------

Weight

Weight:	1.800 lbs.
----------------	------------

Included Parts

Included Parts:	4 Screws (10x32); 4 Screws (12x24); 1 Printable LabelFlex Half-Sheet; 1 Rear Cable Management Bar, 1 Installation Guide
------------------------	---

Packaging

Packaging:	Individually packaged in a cardboard box.
-------------------	---

Mechanical Characteristics (Connectivity)

Footprint/Type:	MDVO-Style
Storage Temperature Range:	-40°C To +70°C
Installation Temperature Range:	-10°C To +60°C
Operating Temperature Range:	-10°C To +60°C

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	07/01/2006
MIL Order #39 (China RoHS):	EUP 50
Safety Listing:	ACA, Bi-national Standard Listed

Suitability

Suitability - Indoor:	Yes
------------------------------	-----

Notes (Overall)

Notes: For proper installation refer to Installation Guide PX103340 included with the product or visit our web site at <http://www.belden.com>

AX101458 Faceplates and Panels - FLEX Patch Panel - MDVO

Product Family

Part Numbers:

Description	Item Number
AngleFlex PP 1U24P, Black	AX103248
AngleFlex PP 2U48P, Black	AX103249
Flex PP 1U24P, Black	AX101456
Flex PP 2U48P, Black	AX101458
AngleFlex PP 1U24P CAT6+ Coupler, Black	AX104568
AngleFlex PP 1U24P 10GX Coupler, Black	AX104569
AngleFlex PP 2U48P CAT6+ Coupler, Black	AX104570
AngleFlex PP 2U48P 10GX Coupler, Black	AX104571

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
AX101458	1 EA	1.895 LB			FLEX PATCH PANEL 48-P 2U BLK

Revision Number: 0 Revision Date: 05-31-2009

© 2017 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.