

**Model: X2C4000BP/G**



## **Xvision PRO-HD Professional 4 Megapixel H265 IR Bullet IP Camera, 20m IR, Video Analytics, White/Grey**

|                                  |                                            |
|----------------------------------|--------------------------------------------|
| Brand                            | Xvision Pro-HD                             |
| Model Number                     | X2C4000BP/G                                |
| Style                            | High Definition Varifocal Bullet Camera    |
| Weather Resistant                | Yes (IP66)                                 |
| Vandal Resistant                 | No                                         |
| Motorised Panning                | No                                         |
| Motorised Tilting                | No                                         |
| Digital Zoom                     | No                                         |
| Audio                            | No                                         |
| Mounting Type                    | Wall or Ceiling                            |
| Product Dimensions (WxHxD) in mm | 68x67x196                                  |
| Product Weight                   | 0.70Kg                                     |
| Warranty                         | 1 Year Warranty (Optional 3 Year Warranty) |

|                                 |                                                                                                                                                                  |
|---------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Image Sensor Type               | 1/2.9" Sony CMOS                                                                                                                                                 |
| Image Sensor Resolution         | 4 Mega Pixel                                                                                                                                                     |
| Minimum Illumination            | 0.0001 Lux (0 Lux IR On)                                                                                                                                         |
| Night Vision                    | 20m IR Night Vision                                                                                                                                              |
| Other Features                  | <div> Automatic White Balance<br/> Automatic Gain Control<br/> Automatic Electronic Iris<br/> DNR (Digital Noise Reduction)<br/> WDR (Wide Dynamic Range) </div> |
| Lens                            | 3.6mm                                                                                                                                                            |
| Viewing Angle                   | 78°                                                                                                                                                              |
| Video Compression               | H.265                                                                                                                                                            |
| Video Streams                   | 1024Kbps-6144Kbps                                                                                                                                                |
| Stream Types                    | Complex Stream/Video Stream                                                                                                                                      |
| Video Resolutions & Frame Rates | 1228x1712 @20fps                                                                                                                                                 |
| Network Connection              | RJ45 Socket (10/100 BASE-T)                                                                                                                                      |
| Wi-Fi Support                   | No                                                                                                                                                               |
| Network Protocols Supported     | TCP/IP, UDP, HTTP, DHCP, RTP/RTSP, DNS, DDNS, NTP, PPPoE, UPNP, SMTP                                                                                             |
| Browser Support                 | Internet Explorer                                                                                                                                                |
| Mobile Phone Support            | Android, iPhone                                                                                                                                                  |
| User Authentication             | Yes                                                                                                                                                              |
| Simultaneous Viewers            | 10                                                                                                                                                               |
| Power Over Ethernet             | Yes                                                                                                                                                              |
| Operating Voltage               | 12V DC                                                                                                                                                           |
| Power Consumption               | <5W                                                                                                                                                              |
| Motion Detection                | No                                                                                                                                                               |
| Presents                        | No                                                                                                                                                               |
| Guard Tours                     | No                                                                                                                                                               |
| Email Alerts                    | Yes                                                                                                                                                              |

|                       |                                                                                                                       |
|-----------------------|-----------------------------------------------------------------------------------------------------------------------|
| On Board Recording    | No                                                                                                                    |
| Alarms                | No                                                                                                                    |
| Video Analytics       | Perimeter Intrusion<br>Line Crossing<br>Stationary Object<br>Pedestrian Detection<br>Face Detection<br>Cross Counting |
| Multi Camera Software | Yes                                                                                                                   |