


K-31S & K-31SL Wall Mount Plug

Socket Contacts



K-31S (small flange) and K-31SL (large flange)

Order Number	For K-31S and K-31SL				For K-31S			For K-31SL		
	D	E	L	A THD.	R	S	T	R	S	T
	$\pm 1/64$	$\pm 1/64$	$\pm 3/64$		$\pm .005$	$\pm 1/64$	$\pm .005$	$\pm .005$	$\pm 1/64$	$\pm .005$
WK-(*)-31S	1-3/64	7/16	1-3/16	7/8-6	.730	15/16	.120	.972	1-5/16	.144
GK-(*)-31S	1-23/64	7/16	1-7/32	1-3/16-6	.972	1-1/4	.120	1.192	1-9/16	.169
SK-(*)-31S	1-15/32	7/16	1-7/32	1-5/16-6	1.038	1-3/8	.120	1.280	1-11/16	.169
NK-(*)-31S	1-47/64	7/16	1-7/32	1-9/16-6	1.259	1-5/8	.169	1.500	1-15/16	.169
FK-(*)-31S	2-1/64	7/16	1-1/4	1-13/16-6	1.502	1-7/8	.169	1.678	2-1/8	.169
LK-(*)-31S	2-7/8	1/2	1-13/32	2-1/2-6	2.077	2-9/16	.169	2.210	2-7/8	.169

For K-31SL (large flange), add "L" to nomenclature, e.g., WK-(*)-31S becomes WK-(*)-31SL. Large flange most popular.

* Add contact arrangement.


Other Products

Dust Caps

Metal threaded dust caps with chain, or low cost, press-fit plastic dust caps are available.

SHELL SIZE	FOR PLUGS		FOR RECEPTACLES	
	METAL W/CHAIN	PLASTIC	METAL W/CHAIN	PLASTIC
WK	WK-59A-2	WK-P	WK-60A-2	WK-R
GK	GK-59A-2	GK-P	GK-60A-2	GK-R
SK	SK-59A-2	SK-P	SK-60A-2	SK-R
NK	NK-59A-2	NK-P	NK-60A-2	NK-R
FK	FK-59A-2	FK-P	FK-60A-2	FK-R
LK	LK-59A-2	LK-P	LK-60A-2	LK-R

Barrel Extensions



SHELL SIZE	PART NUMBER	LENGTH
SK	019961-0001	1 7/32"
NK	019961-0014	1/2"
	019961-0021	3/4"
	019961-0006	1 1/8"
FK	019961-0003	1 7/32"
	019961-0016	1"
LK	019961-0012	1"