

PCRS_LCUX_LCUX_A221T_XX.X_SS

Description

Duplex patch cord, LC uniboot push-pull XD to LC uniboot push-pull XD, UPC, duplex round 2.1mm_yellow, SM G.657.A2, A-B / B-A



Features	Features
- High mechanical stability	
- Colour coded boot for good visibility also in mated condition	

Technical Data

General Data

Description	Values
General Typ	Duplex LC patch cord
Operation temperature (in Work)	-45 up to 85
Polarity	A-B / B-A straight polarity (standard)
RoHS compliant 2001/65/EU	Yes
REACH compliant	Yes

Connector left

Description	Values
Connector typ	LC-XD duplex Uniboot
Polish	PC
Color Housing	Black
Color Clip	Blue
Color Boot	Black / Black
Design connector acc. To	IEC 61754-20, TIA 604-10-A
Performance class H+S	S
Return Loss	>50 dB
Durability	1000
Tensile load	70 N
Tensile load acc. To GR-326-COR	Fullfiled

Connector right


Description	Values
Connector typ	LC-XD duplex Uniboot
Polish	PC
Color Housing	Black
Color Clip	Blue
Design connector acc. To	IEC 61754-20, TIA 604-10-A
Performance class H+S	1S
Return Loss	>50
Durability	1000
Tensile load	70 N
Tensile load acc. To GR-326-COR	Fullfiled

Cable

Description	Values
Cable typ	Riser Cable

PCRS_LCUX_LCUX_A221T_XX.X_SS

Fiber count	2
Fiber	2 x 0.6mm
Fiber typ	E9/125-SM G.657.A2
Outer diameter	2.1 mm
Outer jacket material	Jacket material according to UL 94V-0
Outer jacket color	Yellow



Ordering information

Attenuation (m)	Item number	Description
1.0	85016597	PCRS_LCUX_LCUX_A221T_01.0_SS
1.5	85023034	PCRS_LCUX_LCUX_A221T_01.5_SS
2.0	85016599	PCRS_LCUX_LCUX_A221T_02.0_SS
2.5	85025973	PCRS_LCUX_LCUX_A221T_02.5_SS
3.0	85016600	PCRS_LCUX_LCUX_A221T_03.0_SS
3.5	85020818	PCRS_LCUX_LCUX_A221T_03.5_SS
4.0	85019951	PCRS_LCUX_LCUX_A221T_04.0_SS
4.5	85025974	PCRS_LCUX_LCUX_A221T_04.5_SS
5.0	85016601	PCRS_LCUX_LCUX_A221T_05.0_SS
5.5	85025975	PCRS_LCUX_LCUX_A221T_05.5_SS
6.0	85020819	PCRS_LCUX_LCUX_A221T_06.0_SS
7.0	85020820	PCRS_LCUX_LCUX_A221T_07.0_SS
10.0	85016602	PCRS_LCUX_LCUX_A221T_10.0_SS
15.0	85020821	PCRS_LCUX_LCUX_A221T_15.0_SS
20.0	85020822	PCRS_LCUX_LCUX_A221T_20.0_SS
25.0	85025976	PCRS_LCUX_LCUX_A221T_25.0_SS
30.0	85025977	PCRS_LCUX_LCUX_A221T_30.0_SS