

General Information

Extended Product Type:	FED2.L
Product ID:	1SNA291311R2300
EAN:	3472592913117
Catalog Description:	FED2.L Separator end section Grey
Long Description:	FED2.L - Separator end section - Grey - 4mm Spacing.

Additional Information

ABB Industrial IT Suite:	Control IT
Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
Ambient Temperature:	-5 ... +40 °C
Color:	Grey
Country of Origin:	France (FR)
Customs Tariff Number:	39269097
EAN:	3472592913117
ETIM 4:	EC000886 - Endplate and partition plate for terminal block
ETIM 5:	EC000886 - Endplate and partition plate for terminal block
ETIM 6:	EC000886 - Endplate and partition plate for terminal block
Environmental Information:	1SND220090E1000
Function:	Separator end section
IIT Publishing Status:	Level 0 - Information enabled
Industrial IT Certification Level:	0
Insulation Material:	Polyamide
Invoice Description:	FED2.L Separator end section Grey
Minimum Order Quantity:	20 piece
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Object Classification Code:	X
Order Multiple:	20 piece
Package Level 1 EAN:	3472592913117
Package Level 1 Gross Weight:	0.038 kg
Package Level 1 Length:	250 mm
Package Level 1 Units:	20 piece
Package Level 1 Width:	168 mm
Package Level 2 Units:	1500 piece
Package Level 3 Units:	72000 piece
Product Main Type:	FED2.L
Product Name:	End Section
Product Net Depth:	24.5 mm
Product Net Height:	33 mm
Product Net Weight:	1.9 g
Product Net Width:	4 mm
Product Packing Type:	Bag
RoHS Date:	18 08 2005
RoHS Information:	1SND220478E0000

RoHS information:

13ND230470F0202

RoHS Status: Following EU Directive 2002/95/EC August 18, 2005 and amendment

Selling Unit of Measure: piece

Short Description: Separator end section FED2.L

Spacing: 4 mm

Suitable For:
DB2.5/10.4L
DB2.5/5.2L
DH2.5/10.4L
DH2.5/5.2L
DR2.5/10.4L
DR2.5/5.2L
DS2.5/10.4L
DS2.5/5.2L

