

## General Information

<b>Extended Product Type:</b>	FED1.L
<b>Product ID:</b>	1SNA291301R0200
<b>EAN:</b>	3472592913018
<b>Catalog Description:</b>	FED1.L End Sections Grey
<b>Long Description:</b>	FED1.L - End Sections - Grey - 1.5mm Spacing.

## Additional Information

<b>ABB Industrial IT Suite:</b>	Control IT
<b>Ambient Air Temperature:</b>	Operation -55 ... +110 °C Storage -55 ... +110 °C
<b>Ambient Temperature:</b>	-5 ... +40 °C
<b>Color:</b>	Grey
<b>Country of Origin:</b>	France (FR)
<b>Customs Tariff Number:</b>	39269097
<b>EAN:</b>	3472592913018
<b>ETIM 4:</b>	EC000886 - Endplate and partition plate for terminal block
<b>ETIM 5:</b>	EC000886 - Endplate and partition plate for terminal block
<b>ETIM 6:</b>	EC000886 - Endplate and partition plate for terminal block
<b>Environmental Information:</b>	1SND220090E1000
<b>Function:</b>	End Sections
<b>IIT Publishing Status:</b>	Level 0 - Information enabled
<b>Industrial IT Certification Level:</b>	0
<b>Insulation Material:</b>	Polyamide
<b>Invoice Description:</b>	FED1.L End Sections Grey
<b>Minimum Order Quantity:</b>	20 piece
<b>Mounting on DIN Rail:</b>	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
<b>Object Classification Code:</b>	X
<b>Order Multiple:</b>	20 piece
<b>Package Level 1 EAN:</b>	3472592913018
<b>Package Level 1 Gross Weight:</b>	0.028 kg
<b>Package Level 1 Length:</b>	250 mm
<b>Package Level 1 Units:</b>	20 piece
<b>Package Level 1 Width:</b>	168 mm
<b>Package Level 2 Units:</b>	700 piece
<b>Package Level 3 Units:</b>	33600 piece
<b>Product Main Type:</b>	FED1.L
<b>Product Name:</b>	End Section
<b>Product Net Depth:</b>	24.5 mm
<b>Product Net Height:</b>	33 mm
<b>Product Net Weight:</b>	1.4 g
<b>Product Net Width:</b>	1.5 mm
<b>Product Packing Type:</b>	Bag
<b>RoHS Date:</b>	18 08 2005
<b>RoHS Information:</b>	1SND220090E1000

RoHS information:

13ND230470F0202

**RoHS Status:** Following EU Directive 2002/95/EC August 18, 2005 and amendment

**Selling Unit of Measure:** piece

**Short Description:** End Sections FED1.L

**Spacing:** 1.5 mm

**Suitable For:**  
DH2.5/10.4L  
DH2.5/5.2L  
DR2.5/10.4L  
DR2.5/10.P.4L  
DR2.5/5.2L  
DS2.5/10.4L  
DS2.5/5.2L

