

Power It! 6-Outlet Safety Power Strip, 9-ft. Cord & Clip, Hang Holes, Safety Covers, GFCI Plug

MODEL NUMBER: TLM609GF



Highlights

- 6 outlets (including transformer outlets and 4 safety covers)
- 9 ft. cord with GFCI plug
- Cord wrap with hang holes
- Rugged metal case

Package Includes

- TLM609GF Safety Power Strip
- 4 safety covers
- Owner's manual

Description

This Tripp Lite power strip is designed to safely distribute power to connected equipment in harsh environments. It provides a convenient source for multiple outlets wherever they're needed. 6 outlets distribute AC power to a wide range of power tools, drill presses, air compressors, power sanders and more. Convenient transformer outlets accommodate multiple transformers without blocking other outlets. A 9 ft. grounded cord with integrated cord clip reaches distant outlets. A GFCI plug protects users from electrical shock in wet or humid environments. A lighted on/off switch provides power control over connected equipment. 4 safety covers shield unused outlets from debris and accidental contact. A rugged metal case stands up to the harshest environments. Built-in cord wrap with hang holes provides convenient cord management. Integrated keyhole slots on bottom panel provide convenient wall/desk mounting. Its bright yellow color alerts you and others that power cords and tools are in use.

Features

- 6 outlets distribute AC power to a wide range of band saws, drill presses, air compressors, power sanders and more.
- Convenient transformer outlets accommodate multiple transformers without blocking other outlets.
- A 9 ft. grounded cord with integrated cord clip reaches distant outlets.
- A GFCI plug protects users from electrical shock in wet or humid environments.
- A lighted on/off switch with integrated 15 amp circuit breaker provides power control and overload protection over connected equipment.
- 4 safety covers shield unused outlets from debris and accidental contact.
- A rugged metal case stands up to the harshest environments.
- Built-in cord wrap with hang holes provides convenient cord management.
- Integrated keyhole slots on bottom panel provide convenient wall/desk mounting.
- Its bright yellow color alerts you and others that power cords and tools are in use.
- OSHA color guidelines, outlined in Document 1910.145, alert users to hazardous situations, which may cause minor or moderate injury. This Tripp Lite product complies with those guidelines.

Specifications



OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Overload Protection	GFCI plug
Transformer Accommodation	Yes (2)
Outlet Safety Covers	Yes (4)
Outlet Orientation	Single row
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V, 15A
Input Connection Type	GFCI 5-15P
Input Plug Features	Integrated cord clip plus GFCI breaker
Input Cord Length (ft.)	9
Input Cord Length (m)	2.74
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
USER INTERFACE, ALERTS & CONTROLS	
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch
PHYSICAL	
Shipping Dimensions (hwd / in.)	16.17 x 7.10 x 2.7
Shipping Dimensions (hwd / cm)	41.07 x 18.03 x 6.86
Shipping Weight (lbs.)	3.33
Shipping Weight (kg)	1.51
Unit Dimensions (hwd / in.)	15.97 x 3.07 x 1.61
Unit Dimensions (hwd / cm)	40.56 x 7.80 x 4.09
Unit Weight (lbs.)	3.24
Unit Weight (kg)	1.47
Material of Construction	All-metal
Integrated Keyhole Mounting Tabs	Yes
Receptacle Color	black
Color (AC Line Cord)	yellow



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Outlets Measurement (Center to Center)	Distance between standard outlets = 30.40mm; Distance between standard outlets and transformer outlets = 45mm
Keyhole Slot Mounting Measurement (Center to Center)	209.55mm
CERTIFICATIONS	
Approvals	cULus, RoHS
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>