

High Speed HDMI Easy Pull Cable, Ultra HD 4K x 2K, Digital Video with Audio (M/M), 25-ft.

MODEL NUMBER: P568-025-EZ



Description

Tripp Lite's 25 ft. High Speed HDMI Easy Pull Monitor Cable w/ Connectors makes running long length video cables a snap. The pull-apart design allows the cable to be run through conduit or other tight areas that a HDMI connector wouldn't fit through. Diameter of the circular DIN end is only 7/8". Circular Easy Pull connector is threaded to ensure maximum security once the cable is reattached. Double shielding (foil and braid) provides maximum EMI/RFI protection. Both HDMI male ends are molded and have integral strain relief to provide long life. UL20276 Digital Video Cable supports 1080p and Ultra HD 4K x 2K. In most applications, a signal booster (B122-000-60) will need to be used with this cable to ensure a signal strong enough for your display.

Features

- Two-piece design runs through conduit or other tight areas
- Threaded circular DIN connector provides secure reattachment
- Superior-molded cables with foil and braid shielding for maximum EMI/RFI protection
- High quality quad-shielded cable with Gold connectors and pins
- Bandwidth up to 18 Gbps Full 1080p resolution
- Supports Ultra HD 4K x 2K
- High Speed HDMI and HDCP compliant
- In most applications, a signal booster (B122-000-60) will need to be used with this cable to ensure a signal strong enough for your display
- HDMI male to male molded connectors
- UL20276 Digital Video Cable
- Supports Ultra High Definition (UHD) 4Kx2K video resolutions up to 3840 x 2160

Specifications

INPUT

Highlights

- Two-piece design runs through conduit or other tight areas
- Threaded circular DIN connector provides secure reattachment
- Superior-molded cables with foil and braid shielding for maximum EMI/RFI protection
- Bandwidth up to 18 Gbps Full 1080p resolution
- High Speed HDMI and HDCP compliant
- In most applications, a signal booster (B122-000-60) will need to be used with this cable to ensure a signal strong enough for your display
- Supports Ultra High Definition (UHD) 4Kx2K video resolutions up to 3840 x 2160

Package Includes

 High Speed HDMI Easy Pull Cable, Ultra HD 4K x 2K, Digital Video with Audio (M/M), 25-ft.



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (ft.)	25
Cable Length (m)	7.6
PHYSICAL	
Color	Black
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	HDMI (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies