

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0987891201](#)  
**Status:** **Active**  
**Overview:** NSCC - New Standard Casing Contact  
**Description:** NSCC Single Part, Unsealed, 1.50mm, Male Housing, 10 Circuits, Dual Row, Black

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Application Specification AS-98788-003-FR (PDF)</a>
<a href="#">Application Specification AS-98788-002-001 (PDF)</a>	<a href="#">Packaging Specification PK-98789-001 (PDF)</a>
<a href="#">Application Specification AS-98788-003-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Crimp Housings
Series	<a href="#">98789</a>
Application	Power, Wire-to-Wire
Application Tooling Part Link	63812-1200
Application Tooling Part Link	63813-5700
Overview	<a href="#">NSCC - New Standard Casing Contact</a>
Product Name	NSCC
UPC	822348803408

**Physical**

Circuits (maximum)	10
Circuits Detail	10x1.5mm female terminal
Color - Resin	Black
Gender	Plug
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Resin	Polyester
Net Weight	11.520/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.25mm
Pitch - Termination Interface	6.00mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40°C to +120°C

**Solder Process Data**

Lead-free Process Capability	N/A
------------------------------	-----

**Material Info**

Engineering Number	09211EV10F1
--------------------	-------------

**Reference - Drawing Numbers**

Application Specification	AS-98788-002-001, AS-98788-003-001, AS-98788-003-FR
Packaging Specification	PK-98789-001
Sales Drawing	SD-98789-003



*Series image - Reference only*

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/30/2017 (7 July 2017)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

[98789](#) Series

**Mates With**

[98788-1201](#) 1.50mm Pitch NSCC, Wire-to-Wire, Housing

**Use With**

Sicma 1.5 and 2.8mm Male Terminals for Single Wire Seal from FCI