

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0988211061

Status:

Active

Overview:

NSCC - New Standard Casing Contact

Description:

NSCC, Receptacle Connector Hybrid, Single Part, Unsealed 6 Circuits Black

Documents:

3D Model

Application Specification AS-98821-001-001 (PDF)

Drawing (PDF)

Packaging Specification PK-31301-635 (PDF)

Product Specification PS-98821-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Crimp Housings

Series

98821

Application

Power, Wire-to-Wire

Application Tooling Part Link

63813-3800

Overview

NSCC - New Standard Casing Contact

Product Name

NSCC

UPC

822348761401

Physical

Breakaway

No

Circuits (maximum)

6

Circuits Detail

4 x 1.5 + 2 x 2.8

Color - Resin

Black

Gender

Receptacle

Glow-Wire Compliant

No

Keying to Mating Part

Yes

Lock to Mating Part

Yes

Material - Resin

Polyester

Net Weight

3.490/g

Number of Rows

1

Packaging Type

Bag

Panel Mount

No

Pitch - Mating Interface

3.33mm, 4.20mm, 5.00mm

Pitch - Termination Interface

3.33mm, 4.20mm, 5.00mm

Polarized to Mating Part

Yes

Ports

1

Stackable

No

Temperature Range - Operating

-40°C to +85°C

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Engineering Number

010401321

Reference - Drawing Numbers

Application Specification

AS-98821-001-001

Packaging Specification

PK-31301-635

Product Specification

PS-98821-001-001

Sales Drawing

SD-98820-002, SD-98821-002



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -

ED/30/2017 (7 July

2017)

Halogen-Free

Status

Not Relevant

Need more information on product

environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any

non-product compliance questions.

China ROHS

Not Relevant

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

98821 Series

Mates With

98825 NSCC, or Counterpart per Interface

Drawing, Contact Molex

Application Tooling | FAQ

Tooling specifications and manuals are

found by selecting the products below.

Crimp Height Specifications are then

contained in the Application Tooling

Specification document.

Global

Description

Product #

Extractor Tool for 0638133800

Unsealed Receptacle

Connectors

This document was generated on 08/02/2017

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION