







Gel: UL 94-HB 

Operating temperature 

Installation temperature:   
-40°C / +50°C

Fully submersible 

Can be used underground 



**IPX8**  
OFFICIALLY TESTED 

**GEL BOX LINE**  
*a simple way  
to bring indoor  
connectors outdoors*

# Gel Box Line


Pre-filled gel accessories for sealing, protecting and making safe electrical connections

- To put household systems in order
- For civil and industrial connections
- Also for submersible use
- Non-toxic and with no shelf life
- Versatile and ready to use
- Designed with dimensions suitable for the most commonly used connectors







**JOULE**



**ISAAC**



**KELVIN**



**PASCAL**



## Isaac



Product	Description	Package	A x B x C (mm)
Isaac 4	x 4 pcs	Blister	30 x 27 x 23
Isaac 4 P30	x 30 pcs	Box	
Isaac 4 MP *	x 50 pcs	Multipack	

IDEAL FOR (or similar):



\* Also available the flame retardant version in the following colours: yellow, orange, blue or black.



## Pascal



Product	Description	Package	A x B x C (mm)
Pascal 6	x 2 pcs	Blister	36 x 37 x 26
Pascal 6 P15	x 15 pcs	Box	
Pascal 6 MP *	x 25 pcs	Multipack	

IDEAL FOR (or similar):



\* Also available the flame retardant version in the following colours: yellow, orange, blue or black.





### Watt



Product	Description	Package	A x B x C (mm)
Watt	x 2 pcs	Blister	30 x 42 x 26
Watt P15	x 15 pcs	Box	
Watt MP *	x 25 pcs	Multipack	

IDEAL FOR (or similar):



3x 2.5 mm<sup>2</sup>



2x + 2x 2.5 mm<sup>2</sup>



5x 2.5 mm<sup>2</sup>



2x + 2x 4 mm<sup>2</sup>




5x 4 mm<sup>2</sup>

\* Also available the flame retardant version in the following colours: yellow, orange, blue or black.



### Joule



Product	Description	Package	A x B x C (mm)
Joule	x 1 pcs	Blister	33 x 52 x 26
Joule MP *	x 20 pcs	Multipack	

IDEAL FOR (or similar):



2x + 2x + 2x 2.5 mm<sup>2</sup>




2x + 2x + 2x 4 mm<sup>2</sup>

\* Also available the flame retardant version in the following colours: yellow, orange, blue or black.



### Kelvin



Product	Description	Package	A x B x C (mm)
Kelvin	x 1 pcs	Blister	52 x 53 x 29
Kelvin P9	x 9 pcs	Box	
Kelvin MP *	x 20 pcs	Multipack	

IDEAL FOR (or similar):



3x 6 mm<sup>2</sup>



3x 6 mm<sup>2</sup>

\* Also available the flame retardant version in the following colours: yellow, orange, blue or black.

