



DeoxIT® D5 Spray

Contact Cleaner & Rejuvenator

| | |
|------------------------|---|
| Part No.: | D5S-6 |
| Formulation: | 5% DeoxIT® D100L |
| | 75% odorless mineral spirits (64742-88-7) |
| | 20% hydrocarbon propellant (75-28-5, 74-98-6) |
| Container Size: | 142 g |



Product Description:

Contact cleaner, rejuvenator, conductivity enhancer and lubricant; dissolves oxidation and corrosion on metal surfaces, fills in microscopic gaps and reseals surface for better contact to enhance flow of electricity. Improves connector performance/reliability.
 Temperature range: -34 to +200°C.

Features/Benefits:

Spray - Flushing Action, Slow Dry and Safe on Plastics.

DeoxIT® D100L concentrate has approximately 20% chemical cleaning action. Excellent cleaning/deoxidizing, good protection, no ozone depletion. Improves conductivity and reduces intermittent connections. Reduces arcing, RFI, wear and abrasion.

Cleaner Audio - Clearer Video - Reliable Data.

Other Applicators:

| | | | | |
|--------------|------|------------------|----------|--------------|
| D5MS-15 | 5% | mini-spray | 14 g | flammable |
| DN5S-6N | 5% | spray | 163 g | nonflammable |
| DN5MS-15 | 5% | mini-spray | 14 g | nonflammable |
| D100S-2 | 100% | spray | 57g | nonflammable |
| D100P | 100% | pen | 6 mL | nonflammable |
| D50W | 100% | wipes | 50 count | nonflammable |
| D100L-2DB | 100% | brush | 7.4 mL | nonflammable |
| D100L-25C | 100% | needle dispenser | 25 mL | nonflammable |
| D100L (bulk) | 100% | bottle/drum | assort. | nonflammable |
| D5L (bulk) | 5% | bottle/drum | assort. | flammable |

DeoxIT® Essential Reference:

DeoxIT® - *Brings old systems back to life!*

DeoxIT® GOLD - *Maintains new system performance!*

DeoxIT® SHIELD - *Maintains new system performance for severe environments!*

Shipping Information:

Hazardous: Y - ORMD

Other Information:

RoHS Compliant: YES

D5S-6 MSDS Link: <http://store.caig.com/app/site/media/sitemedia.nl/id.906/f>

DeoxIT® Product Sheet: <http://store.caig.com/app/site/media/sitemedia.nl/id.775/f>

MentorCard Link: http://www.caig.com/pdf/MentorCards_2006_av.pdf

MANUFACTURER DISCLAIMER:

To the best of our knowledge, the information contained herein is accurate. However, neither CAIG Laboratories, Inc., or any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. All materials may present unknown hazards and should be used with caution. In particular, improper use of our products and their inappropriate combination with other products and substances may produce harmful results which cannot be anticipated. Final determination of the suitability of any material is the sole responsibility of the user. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that may exist. All service performed on internal parts and equipment should be provided by qualified technicians.

Contact Information:



North America

CAIG Laboratories, Inc.
12200 Thatcher Court
Poway, CA 92064 USA
Tel: (858) 486-8388
Fax: (858) 486-8398

Website

www.caig.com

General email

caig123@caig.com

Technical email

tech@caig.com