



# EcoLine™ Cleaner/Degreaser

Light Duty Degreaser

1620

## Introduction

This Cleaner/Degreaser is designed for cleaning electronic and electrical equipment, machinery and metal parts. Its rapid evaporation and complete compatibility with plastics make it the perfect choice for light duty cleaning.

### Features / Benefits

- EPA SNAP Approved
- Non-Ozone Depleting
- Safe on Plastics
- Zero Residue
- Rapidly Evaporating
- Non-Corrosive

### Physical Properties

<b>Boiling Point</b>	52°C / 136.5°F
<b>Flash Point (TCC)</b>	-15°F
<b>Evaporation Rate</b>	>1
<b>Surface Tension</b>	
<b>Kauri-Butanol (KB Value)</b>	

## Chemical Components

Isopropanol.....	(67-63-0)	8-12%
Denatured Alcohol.....	(64-17-5)	18-25%
2-Methyl-2-Propanol.....	(75-65-0)	<<1%
Carbon Dioxide.....	(124-38-9)	1-4%
Hexane Isomers Consisting of:		
n-Hexane.....	(110-54-3)	39-43%
Methylcycle pentane.....	(96-37-7)	8-10%
Methyl pentane.....	varies	12-18%
Acetic Acid, Propyl Ester.....	(109-60-4)	< 3%

## Plastic Compatibility

Material	Compatibility	Material	Compatibility
ABS	Excellent	PMMA	Excellent
Nylon	Excellent	POM	Excellent
Lexan	Excellent	PP	Excellent
HDPE	Excellent	PS	Excellent
CDPE	Excellent	PTFE	Excellent
C. E. Phenolic	Excellent	PVC	Excellent

## Environmental Policy

---

Techspray® is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

## Packaging and Availability

---

EcoLine™ Cleaner/Degreaser may be ordered in the following container sizes:

1620-10S	10 Ounce Aerosol
1620-GS	1 Gallon Bladder

## Resources

---

Techspray® products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray® products in the United States, call the technical sales department at 800-858-4043, email [tsales@techspray.com](mailto:tsales@techspray.com) or visit our web site at: [www.techspray.com](http://www.techspray.com).

North America  
Tech Spray L.P.  
P.O. Box 949  
Amarillo, TX 79105  
800-858-4043  
email: [tsales@techspray.com](mailto:tsales@techspray.com)

Europe  
Techspray International  
UNIT 4, 44/46 Bunyan Road, Kempston  
Bedford MK42 8HL United Kingdom  
+44 (0) 1234 855443  
email: [tseurope@techspray.com](mailto:tseurope@techspray.com)

Countries Outside US  
Call to locate a distributor  
in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray® be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.



Tech Spray, L.P.  
P.O. Box 949  
Amarillo, TX 79105  
[www.techspray.com](http://www.techspray.com)

[English MSDS](#)  
[French MSDS](#)  
[German MSDS](#)  
[Italian MSDS](#)  
[Spanish MSDS](#)

