

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2018460040](#)  
**Status:** **Active**  
**Overview:** [MultiCat Power Connectors with Precision-Machined Contacts](#)  
**Description:** MultiCat™ Receptacle Terminal, Gold over Nickel Phosphorus Plating, 8-10 AWG

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Test Summary 2018400000-TS-000 (PDF)</a>
<a href="#">Product Specification 2018400000-PS-000 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification 2018400000-AS-000 (PDF)</a>	<a href="#">Product Literature (PDF)</a>
<a href="#">Packaging Specification 2018460001-PK (PDF)</a>	



Series image - Reference only

**General**

Product Family	Crimp Terminals
Series	<a href="#">201846</a>
Application	Power
Crimp Quality Equipment	Yes
Overview	<a href="#">MultiCat Power Connectors with Precision-Machined Contacts</a>
Product Literature Order No	987651-4731
Product Name	MultiCat™
UPC	889056747479

**Physical**

Durability (mating cycles max)	500
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Gold over Nickel Phosphorus
Material - Plating Termination	Gold over Nickel
Packaging Type	Bag
Plating min - Mating	0.100µm
Plating min - Termination	0.200µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	4.03mm-5.84mm
Wire Size AWG	10, 8
Wire Size mm²	5.26-8.36

**Electrical**

Current - Maximum per Contact	40.0A
Voltage - Maximum	1000V AC

**Material Info**

**Reference - Drawing Numbers**

Application Specification	2018400000-AS-000
Packaging Specification	2018460001-PK
Product Specification	2018400000-PS-000
Sales Drawing	2018460040-000
Test Summary	2018400000-TS-000

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

**Search Parts in this Series**

[201846 Series](#)

**Use With**

[MultiCat™ Inline Receptacle Housing 201841](#)