

## STYLUS® ALKALINE BATTERY-POWERED PEN LIGHT

**MARKET**

**APPLICATIONS:** Law Enforcement, Security, Hardware/Tool, Sporting Goods, Fire & Rescue, Industrial Safety, Occupational Safety, Automotive, Gift, Consumer

**DESCRIPTION:** Ultra-slim pen light with a high intensity LED.  
Perfect for tactical use and covert operation while preserving night vision.


**CASE MATERIAL:** Machined aluminum case with non-slip knurled grip.  
Available in black, gold, silver, red, blue or flag anodized finish.

**DIMENSIONS:** Length: 6.21 in. (15.17 cm)      Diameter: 0.375 in. (0.95 cm)

**WEIGHT:** 1.1 oz (31 grams) with batteries (included with purchase).

**LIGHT SOURCE:** High intensity 5mm LED, impervious to shock with a 100,000 hour lifetime.  
Available in White, Blue (470nm), Red (624nm), Green (527nm), UV (365nm) or IR (880nm).

**LIGHT OUTPUT:** White: 140 candela peak beam intensity, 24m beam distance and 11 lumens measured system output.  
Blue: 110 candela peak beam intensity, 21m beam distance and 2 lumens measured system output.  
Red: 53 candela peak beam intensity, 15m beam distance and 2 lumens measured system output.  
Green: 59 candela peak beam intensity, 15m beam distance and 7 lumens measured system output.  
UV: 3.8 mW measured system output.  
IR: 12 mW/sr measured system output.  
See model for specific LED selection.



**ON/OFF:** Features momentary blink or constant "on" operation.

**RUN TIME:** 24 continuous hours to the 10% lumen output level.





**BATTERY:** 3 "AAAA" size alkaline batteries.

**FEATURES:** High intensity LED.  
Individually serialized for positive identification.  
IPX4 Rated for water resistant operation.  
2 meter impact resistance tested  
Removable pocket clip.  
Glare guard protector included in package.



**APPROVALS\*:**  Class I, Division 1, Groups A, B, C, D, T3C Exia


 II 1G EEx ia IIC T1 - DEMKO 04 ATEX 0410949

 Most models meet applicable European Community Directives.

**WARRANTY:** Streamlight warrants this product to be free of defects for a lifetime of use. We will repair, replace or refund the purchase price, at our option, of any Streamlight product that does not work as a result of a manufacturing defect for as long as you own it. This limited lifetime warranty excludes abuse, battery leakage and normal wear and tear.

**OPTIONAL ACCESSORIES:** Glare Guard, Holster, Lanyard

**PERFORMANCE CURVE**



\* See product for specific ratings.  
All performance claims to ANSI/NEMA FL1-2009 Standard