



# DeoxIT® D100L Liquid

## Contact Cleaner & Rejuvenator

**Part No.:** D100L  
**Formulation:** 100% DeoxIT® D100L



### Container Size:

D100-2C	100%	squeeze tube	2 mL	nonflammable
D100P	100%	pen	6 mL	nonflammable
D50W	100%	wipes	50 count	nonflammable
D100L-2DB	100%	brush	7.4 mL	nonflammable
D100L-25C	100%	needle dispenser	25 mL	nonflammable
D100L-2	100%	bottle	59 mL	nonflammable
D100L-8	100%	bottle	236 mL	nonflammable
D100L-16	100%	bottle	472 mL	nonflammable
D100L-32	100%	bottle	944 mL	nonflammable

### Product Description:

Contact cleaner, rejuvenator, conductivity enhancer and lubricant; dissolves oxidation and corrosion on metal surfaces, fills in microscopic gaps and reseals surface for better contact to enhance flow of electricity. Improves connector performance/reliability.

Temperature range: -34 to +200°C.

**Cleaner Audio - Clearer Video - Reliable Data.**

### Features/Benefits:

**100% Liquid - Safe on Plastics.**

DeoxIT® D100L concentrate has approximately 20% chemical cleaning action.

Excellent cleaning/deoxidizing, good protection, no ozone depletion.

Improves conductivity and reduces intermittent connections.

Reduces arcing, RFI, wear and abrasion.

### Other Applicators:

D5S-6	5%	spray	142 g	flammable
D5MS-15	5%	mini-spray	14 g	flammable
DN5S-6N	5%	spray	163 g	nonflammable
DN5MS-15	5%	mini-spray	14 g	nonflammable
D5L (bulk)	5%	bottle/drum	assort.	flammable

## DeoxIT® Essential Reference:

---

**DeoxIT®** - Brings old systems back to life!

**DeoxIT® GOLD** - Maintains new system performance!

**DeoxIT® SHIELD** - Maintains new system performance for severe environments!

## Shipping Information:

---

Hazardous: No

## Other Information:

---

RoHS Compliant: YES

D100L MSDS Link:

DeoxIT® Product Sheet:

MentorCard Link:

<http://store.caig.com/app/site/media/sitemedia.nl/id.907/.f>

<http://store.caig.com/app/site/media/sitemedia.nl/id.775/.f>

[http://www.caig.com/pdf/MentorCards\\_2006\\_av.pdf](http://www.caig.com/pdf/MentorCards_2006_av.pdf)



## MANUFACTURER DISCLAIMER:

---

To the best of our knowledge, the information contained herein is accurate. However, neither CAIG Laboratories, Inc., or any of its subsidiaries assumes any liability whatsoever for the accuracy or completeness of the information contained herein. All materials may present unknown hazards and should be used with caution. In particular, improper use of our products and their inappropriate combination with other products and substances may produce harmful results which cannot be anticipated. Final determination of the suitability of any material is the sole responsibility of the user. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that may exist. All service performed on internal parts and equipment should be provided by qualified technicians.

## Contact Information:

---



### North America

CAIG Laboratories, Inc.  
12200 Thatcher Court  
Poway, CA 92064 USA  
Tel: (858) 486-8388  
Fax: (858) 486-8398

### Website

[www.caig.com](http://www.caig.com)

### General email

[caig123@caig.com](mailto:caig123@caig.com)

### Technical email

[tech@caig.com](mailto:tech@caig.com)