

General Information

| | |
|--------------------------|---|
| Kit Part Number: | 76650-0057 |
| Description: | Panel Mount Plug and Receptacle, 15 Circuit |
| Application: | Consumer Products, White Goods Application |
| Connector Family: | Standard .093 |
| Solution: | Power Connectors |
| Connector Type: | Wire-to-Wire |
| Number of Pieces: | 36 |
| RoHS: | Yes |

Specifications

| | |
|--------------------------|--------------------|
| Adapter Family: | 15 |
| Current Rating: | 5A |
| Mounting Style: | Panel Mount |
| Orientation: | Receptacles, Plugs |
| Pitch: | 5.03mm (.198") |
| Tool Included: | No |
| Voltage Rating: | 600V |
| Wire Gauge (AWG): | 22-18 |

Product Highlights

Product Highlights

The Standard .093" (2.36mm) is a durable and economical power or signal connector, capable of carrying up to 12 amps per circuit. Tough Nylon housings and robust terminal design create a durable, long lasting product. The Standard .093" products are reliable and offer high value in features and price. These products are an excellent choice for power or signal interconnect applications.

Features and Benefits

- Male and female terminals may be used in either plug or receptacle housings
- Free hanging or panel mount housing version available
- Round terminals may be oriented in any direction for fast assembly

Applications

- Power Supplies
- Appliances
- Gaming Machines
- Vending Machines
- Refrigerators
- Washing Machines
- Copy Machines

Bill of Materials

| Part No. | Qty In Kit | Description | Datasheet | P/N Details | Search Distributors Inventory |
|----------------------------|---------------|---|---------------------------|-------------------------|----------------------------------|
| 02-09-1119 | 17 | 2.36mm (.093") Diameter Crimp Female Socket Terminal, 22-18 ... | Datasheet | Details | Search |
| 02-09-2118 | 17 | .093" Diameter Crimp Male Pin Terminal, 22-18 AWG | Datasheet | Details | Search |
| 03-09-1151 | 1 | 15 Circuit, Panel Mount Nylon Connector Receptacle | Datasheet | Details | Search |
| 03-09-2159 | 1 | 15 Circuit, Panel Mount Nylon Connector Plug | Datasheet | Details | Search |

Recommended Tool

| Part No. | Included in Kit |
|----------------------------|-----------------|
| 63819-1200 | No |
| 11-02-0003 | No |
| 63824-0200 | No |
| 11-03-0006 | No |



76650-0057

RoHS

.093" SERIES

.093" 15 Circuit Conn W/Recpt & Plug
5 Amps / 600 Volts UL & CSA Recognized

