

CONCERT 88

Wireless Systems



Samson's Concert 88 Wireless Systems offer high performance UHF wireless solutions for a variety of applications where the freedom of mobility is a must. Available in handheld, headset, lavalier and guitar configurations, Concert 88 systems are perfect for musicians, business professionals, educators and others looking for stunning sound and versatility without cables.

The frequency-agile Concert 88 system allows for up to 16 systems to operate simultaneously across two frequency bands with up to 300 feet separating the receivers and transmitters. At the core of the system is the CR88 Wireless Receiver. Featuring a true diversity design, the CR88 minimizes signal dropouts during performance. If a dropout does occur, the CR88's tone key and auto mute functions eliminate any background noise until the signal is restored.

The CR88 receiver's front panel provides a Select button for auto syncing receiver and transmitter channels via an infrared signal. The panel also features a 7-segment Channel LED, Volume knob, Power button, two tuned antennas, as well as Audio and Ready indicators, for optimal functionality and monitoring. Balanced XLR and 1/4-inch outputs can be found on the receiver's back panel.

The Concert 88 system is available in four different transmitter configurations: Concert 88 Handheld with the CH88 Handheld Transmitter and CL6 Professional Dynamic Microphone, Concert 88 Headset with the CB88 Beltpack Transmitter and HS5 Headset Microphone, Concert 88 Presentation with the CB88 Beltpack Transmitter and LM5 Lavalier Microphone and Concert 88 Guitar with the CB88 Beltpack Transmitter and GC32 Guitar Cable. Each transmitter, which can operate for up to eight hours on two AA batteries, is engineered to the finest detail to provide the ultimate in sound reproduction in its given application.

With Samson's Concert 88 Wireless Systems, advanced technology and total versatility combine to provide high quality wireless performance wherever you need it.

FEATURES

CONCERT 88 WIRELESS SYSTEMS

- High performance professional UHF wireless system
- Rack mount kit included

CR88 WIRELESS RECEIVER

- True diversity design minimizes dropouts
- Up to 16 systems can be operated simultaneously across two frequency bands
- Tone key and auto mute functions eliminate background noise during dropouts
- Infrared set links the receiver and transmitter channels
- Balanced XLR and 1/4-inch output

WIRELESS TRANSMITTERS

- Available in handheld, headset, lavalier and guitar configurations
- Transmitters offers up to eight hours of battery life using two AA batteries
- 300-foot operating range

CONCERT 88 HANDHELD SYSTEM

UPC...	809164211143, 809164211150
SKU...	SWC88HCL6-C, SWC88HCL6-D
LIST	\$199.99
STREET	\$169.99
HEIGHT	9.75"
WIDTH	11.75"
DEPTH	3.25"
WEIGHT	TBD

CONCERT 88 HEADSET SYSTEM

UPC...	809164211105, 809164211112
SKU...	SWC88BHS5-C, SWC88BHS5-D
LIST	\$199.99
STREET	\$169.99
HEIGHT	9.75"
WIDTH	11.75"
DEPTH	3.25"
WEIGHT	TBD

CONCERT 88 PRESENTATION SYSTEM

UPC...	809164211129, 809164211136
SKU...	SWC88BLM5-C, SWC88BLM5-D
LIST	\$199.99
STREET	\$169.99
HEIGHT	9.75"
WIDTH	11.75"
DEPTH	3.25"
WEIGHT	TBD

CONCERT 88 GUITAR SYSTEM

UPC...	809164211082, 809164211099
SKU...	SWC88BGT-C, SWC88BGT-D
LIST	\$199.99
STREET	\$169.99
HEIGHT	9.75"
WIDTH	11.75"
DEPTH	3.25"
WEIGHT	TBD

* DIMENSIONS AND WEIGHTS BOXED

** MASTER CARTON QUANTITY (ALL): N/A

SAMSON