

**Sunset Vintage Globe 95mm 5W (40W) 1800K 380lm E27 Dimmable Lamp***Partcode: ILGLOBE27D009 / Page: 1***Globe 95mm**

Create a relaxing ambience with an ultra-warm (1800K), dimmable, energy-saving LED filament lamp. The Sunset range has a retro look with tinted amber glass and an eye-catching vintage design.

Built using the latest LED filament technology to deliver an A+ energy rating and 93% energy savings compared to the incandescent lamp it replaces. Enjoy the classic aesthetic look but with an improved lifetime of 15,000 hours.

**Product Details**

Partcode: ILGLOBE27D009

Check Code: 902561

Range Name: Sunset

Product Type: Vintage Decorative

Warranty: 2 Years

CE / RoHS: Yes

**Physical Data**

Lamp Base: E27

Base Type: Edison screw

Globe Type: Globe 95

Globe Finish: Clear

Material: Glass

Construction: Glass shell, Filament Strip

**Physical Data**

Length: 140mm  
Width: 95mm  
Diameter: 95mm  
Weight (Unpackaged Single Unit): 63g  
Lamp or Luminaire Shape: Round  
Lamp Fixing: Pendant, Chandelier, Wall


**Electrical Data**

Voltage Range: 220-240V  
Power Consumption: 5.0 Watts  
Driver included: Yes  
Electric Current: AC  
Ampage: 28.00mA  
Frequency Range: 50/60 Hz  
Power Factor:  $\geq 0.70$   
Wattage Equivalent: 40 Watts  
Dimming: Dimmable  
LVD Certified: Yes  
EN: EN-62560

**Light Data**

Lumens: 380lm  
Lumens per Watt: 76.0lm/W  
Beam Angle: 290°  
Correlated Colour Temperature (CCT): 1,800k  
Colour Rendering Index (CRI):  $\geq 78$   
LED Type: Filament chip  
Instant on - Less than 1 second: Yes  
Lifetime: 15,000 hrs  
Switching Cycles:  $>7,500 X$

## Environmental



Energy Rating: A+

Lowest Operating Temperature: -20 degrees

Maximum Operating Temperature: 45 degrees

IP (Ingress Protection) Rating: IP20

Hg 0% (Mercury Free): Yes

## Packaging



EAN Barcode (unit of 1): 5055788224105

Packaged Weight (Unit of 1): 200g

Length (unit of 1): 101mm

Width (unit of 1): 101mm

Depth (unit of 1): 159mm

**Outer packaging info available on website**

*Product data last updated on: Monday, August 7, 2017 - 14:37*