

**Sunset Vintage ST64 5W (40W) 1800K 380lm B22 Dimmable Lamp***Partcode: ILST64B22D004 / Page: 1***ST64**

Create a relaxing ambience with an ultra-warm (1800K), dimmable, energy-saving LED filament lamp. The Sunset range has a retro look with tinted amber glass and an eye-catching vintage design.

Built using the latest LED filament technology to deliver an A+ energy rating and 93% energy savings compared to the incandescent lamp it replaces. Enjoy the classic aesthetic look but with an improved lifetime of 15,000 hours.

**Product Details**

Partcode: ILST64B22D004

Check Code: 423864

Range Name: Sunset

Product Type: Vintage Decorative

Warranty: 2 Years

CE / RoHS: Yes

**Physical Data**

Lamp Base: B22

Base Type: Bayonet cap

Globe Type: ST64

Globe Finish: Clear

Material: Aluminium, Glass

Construction: Glass shell, filament strip, Aluminium Base

*Partcode: ILST64B22D004 / Page: 2*

### **Physical Data**

Length: 138mm  
Width: 64mm  
Diameter: 64mm  
Weight (Unpackaged Single Unit): 110g  
Lamp or Luminaire Shape: Oval  
Lamp Fixing: Pendant, Chandelier, Wall


### **Electrical Data**

Voltage Range: 220-240V  
Power Consumption: 5.0 Watts  
Driver included: Yes  
Electric Current: AC  
Ampage: 29.00mA  
Frequency Range: 50/60 Hz  
Power Factor:  $\geq 0.70$   
Wattage Equivalent: 33 Watts  
Dimming: Dimmable  
LVD Certified: Yes  
EN: EN-62560

### **Light Data**

Lumens: 380lm  
Lumens per Watt: 76.0lm/W  
Beam Angle: 290°  
Correlated Colour Temperature (CCT): 1,800k  
Colour Rendering Index (CRI):  $\geq 78$   
LED Type: Filament chip  
Instant on - Less than 1 second: Yes  
Lifetime: 15,000 hrs  
Switching Cycles:  $>7,500$  X

## Environmental



Energy Rating: A+

Lowest Operating Temperature: -20 degrees

Maximum Operating Temperature: 45 degrees

IP (Ingress Protection) Rating: IP20

Hg 0% (Mercury Free): Yes

## Packaging



EAN Barcode (unit of 1): 5055788224150

Packaged Weight (Unit of 1): 120g

Length (unit of 1): 72mm

Width (unit of 1): 72mm

Depth (unit of 1): 153mm

**Outer packaging info available on website**

*Product data last updated on: Monday, August 7, 2017 - 14:37*