

**Accessories**  
**ZQV 6/4 GE**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 1429-0  
Fax: +49 5231 14292083  
www.weidmueller.com

**Spring connection with tension clamp Technology**

Tension clamp technology is a universal contact system for all common conductor connection types. Its fantastic level of flexibility makes the tension clamp a profitable alternative connection.

**General ordering data**

Type	ZQV 6/4 GE
Order No.	<a href="#">1627870000</a>
Version	Accessories, Cross-connector, 41 A
GTIN (EAN)	4008190200442
Qty.	60 pc(s).

**Accessories**  
**ZQV 6/4 GE**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 1429-0  
 Fax: +49 5231 14292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Width	3.1 mm	Width (inches)	0.122 inch
Height	30.5 mm	Height (inches)	1.201 inch
Depth	33.96 mm	Depth (inches)	1.337 inch
Net weight	5.48 g		

**Temperatures**

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C
----------------------------------	--------	----------------------------------	--------

**Material data**

Material	Wemid	Colour	Yellow
UL 94 flammability rating	V-0		

**System specifications**

Version	For the terminals	Mounting rail	none
---------	-------------------	---------------	------

**Additional technical data**

Explosion-tested version	Yes	Installation advice	Direct mounting
Type of fixing	Plugged		

**Dimensions**

Pitch in mm (P)	8.1 mm
-----------------	--------

**Rating data**

Rated current	41 A
---------------	------

**Classifications**

ETIM 3.0	EC000489	ETIM 4.0	EC000489
ETIM 5.0	EC000489	ETIM 6.0	EC000489
UNSPSC	30-21-18-01	eClass 5.1	27-14-11-40
eClass 6.2	27-14-11-40	eClass 7.1	27-14-11-40
eClass 8.1	27-14-11-40	eClass 9.0	27-14-11-40
eClass 9.1	27-14-11-40		

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Brochure/Catalogue	<a href="#">CAT 1 TERM 16/17 EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
User Documentation	<a href="#">Beipackzettel_ZDU1.5-ZDU35_ZQV.pdf</a>