

LED light in a particularly slim design!

Slim LED floodlight

Technical highlights

- For wall mounting, indoor and outdoor, IP54
- User-friendly assembly thanks to functional connection box
- Sturdy, state-of-the-art aluminium casing, particularly slim design
- Adjustable holding bracket for assembly
- With 30cm cable and connection box
- This floodlight includes integrated LED lamps
- The lamps cannot be exchanged in floodlight



Technical data

Supply voltage:	230V, 50/60Hz
Cable length:	30cm
Cable designation:	H05RN-F 3G1.0
Colour temperature:	6500K
Colour rendering index:	80
IP class:	IP54
Life cycle LED:	50,000h
Radiation angle:	110°
Swivel range, vertical:	180°
Protection class:	I
Operating temperature:	-10°C ~ +40°C
Colour:	silver



Versions without motion sensor (PIR):

Type designation	L DN 2810 FL DE 3925	L DN 5630 FL DE 3925	L DN 9850 FL DE 3925
Art. no.	1172900100	1172900300	1172900500
EAN	4007123649853	4007123649891	4007123649921
Power	10W	30W	50W
LEDs	28 x 0.36W	56 x 0.5W	98 x 0.5 W
Luminous flux	950lm	2530lm	4750lm
Efficiency, lamp	95 lm/W	84 lm/W	96 lm/W
total energy consumption	9.9kWh / 1000h	30.2kWh / 1000h	49.2kWh / 1000h
Energy efficiency class	A+	A	A+
Dimensions	13.6x14.7x4.1cm	20.2x23.1x3.5cm	23.5x27.7x4.0cm
Weight	0.5kg	1.3kg	2.0kg

Versions with motion sensor (PIR):

Type designation	L DN 2810 FL PIR DE 3925	L DN 5630 FL PIR DE 3925	L DN 9850 FL PIR DE 3925
Art. no.	1172900101	1172900301	1172900501
EAN	4007123649860	4007123649907	4007123649914
Power	10W	30W	50W
LEDs	28 x 0.36W	56 x 0.5W	98 x 0.5 W
Luminous flux	950lm	2530lm	4750lm
Efficiency, lamp	95 lm/W	84 lm/W	96 lm/W
total energy consumption	9.9kWh / 1000h	30.4kWh / 1000h	49.2kWh / 1000h
Energy efficiency class	A+	A	A+
Detection range PIR	max. 12m	max. 12m	max. 12m
Detection angle PIR	90°	90°	90°
Duty-cycle PIR	10sec ~ 5 min	10sec ~ 5 min	10sec ~ 5 min
Swivel range PIR	180° horizontal	180° horizontal	180° horizontal
Dimensions	16.6x14.7x4.3cm	25.2x23.1x4.1cm	29.0x27.7x4.1cm
Weight	0.5kg	1.4kg	2.1kg



Scope of delivery / art. No. / EAN no.

- Packed in a coloured sales cardboard box
- Art. no./ EAN see at top
- PU: 1
- Available from September 2017