

00 21 19 LB S

KNIPEX L-BOXX® Plumbing 52 parts



- Equipped with 52 brand name quality tools, some VDE tested according to DIN EN 60900
- Several boxes can be securely joined together
- Flexible inner partitions
- With two-part tool holder made of hard-wearing polyester fabric
- Tool holders are connected to each other using Velcro
- Handle can be lowered into a hollow in the lid to save space
- Ergonomically shaped handles with additional moulded recess on the side for flexible, convenient handling
- Dimensions, exterior (W x H x D): 442 x 151 x 357 mm; dimensions, interior (W x H x D): 375 x 107 x 311 mm
- Strong box made of impact- and shock-proof ABS plastic

Article No.	00 21 19 LB S
EAN	4003773081630
Net weight g	9400

technical change and errors excepted

L-BOXX® is a registered trademark of Sortimo International GmbH

Content 00 21 19 LB S (25)

Article No.			Quantity	Nominal size	
00 11 01	Knipex	KNIPEX TwinKey®, for all standard cabinets and shut-off systems	1		
26 16 200	Knipex	Snipe Nose Side Cutting Pliers, (Stork Beak Pliers)	1	200 mm	
74 06 180	Knipex	High Leverage Diagonal Cutter	1		
86 03 250	Knipex	Pliers Wrench, pliers and a wrench in a single tool	1		
87 01 250	Knipex	KNIPEX Cobra®, Hightech Water Pump Pliers	1	250 mm	
87 01 400	Knipex	KNIPEX Cobra® XL, Pipe Wrench and Water Pump Pliers	1		
98 20 35	Knipex	Screwdrivers for slotted screws	1		
98 20 55	Knipex	Screwdrivers for slotted screws	1	5,5 mm	
98 26 15	Knipex	Screwdriver for Torx® screws	1		
98 26 20	Knipex	Screwdriver for Torx® screws	1		
98 26 25	Knipex	Screwdriver for Torx® screws	1		
98 24 01	Knipex	Screwdriver for cross recessed screws, Phillips®	1	PH 1	
98 24 02	Knipex	Screwdriver for cross recessed screws, Phillips®	1	PH 2	
361 252 1	Rennsteig	Electrician's Chisel	1	250 x 10 mm	
005655	Wera	Voltage detector, single-pole, 247	1	0,5 x 3,0 x 70 mm	
004018	Wera	8100 SA 8 Zyklop set of metal ratchets, 28 parts	1	1/4"	
003760	Wera	Joker open-end wrench	1	10 x 13 mm	
022086	Wera	set of hex key wrenches	1	1,5 - 10 mm	
90958	Heyco	Express key	1	17 x 19 mm; M 10	
16640003	Heyco	Safety cutter knife	1	18 mm	
101-0300	Picard	Locksmith's hammer	1	300 g	
340 250 1	Rennsteig	Mason's Chisels	1	250 mm	
02281	Stabila	spirit level type 70	1	30 cm	
71510-000	Picard	Metre ruler (yardstick)	1	2 m	
6135-0	Zenten	pipe cutter	1	3 - 35 mm / 1/8 - 1 1/2"	