


H25,0/36 BR



General ordering data

Type	H25,0/36 BR
Order No.	0317100000
Version	Wire end ferrule, insulated, 24 mm, 22 mm, Brown
GTIN (EAN)	4008190049751
Qty.	50 pc(s).
Packaging	loose

Dimensions and weights

Width	36 mm
Width (inches)	1.417 inch
Net weight	1.2 g

Technical data

Version	insulated
---------	-----------

Wire-end ferrules

Collar diameter (D2)	11.2 mm
Colour code	Weidmüller
Conductor cross-section	25 mm ²
Contact surface diameter (D1)	7.3 mm
Contact surface length (L2)	22 mm
L1 in mm	36 mm
Metal sleeve thickness (S1)	0.2 mm

Military designation	T 20A 030 A
Plastic collar thickness (S2)	0.4 mm
Stripping length	24 mm
Wire connection cross section AWG, max.	AWG 3

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	EPLAN, WSCAD, Zuken E3.S

Classifications

ETIM 3.0	EC000005
ETIM 4.0	EC000005
ETIM 5.0	EC000005
ETIM 6.0	EC000005
UNSPSC	31-16-31-02
eClass 5.1	27-40-02-01
eClass 6.2	27-40-02-01
eClass 7.1	27-40-02-01
eClass 8.1	27-40-02-01
eClass 9.0	27-40-02-01
eClass 9.1	27-40-02-01

Approvals

Approvals




ROHS

Conform

UL File Number Search

[E354986](#)

Related products:



Type: H25,0/30 BR
Order No.: 0317000000

Version:
Wire end ferrule, insulated, 18 mm, 16 mm, Brown


Description of article: Wire end ferrule with plastic collar, brown

[PDF data sheet](#) [Add to Inquiry List](#)

Type: H25,0/30D 16 GE
Order No.: 9019280000

Version:
Wire end ferrule, insulated, 18 mm, 16 mm, Yellow

Description of article: Wire end ferrule with plastic collar, yellow




[PDF data sheet](#) [Add to Inquiry List](#)

Type: H25,0/30T SW
Order No.: 9021190000

Version:
Wire end ferrule, insulated, 18 mm, 16 mm, Black

Description of article: Wire-end ferrule




[PDF data sheet](#) [Add to Inquiry List](#)

Type: H25,0/36D GE
Order No.: 9019300000

Version:
Wire end ferrule, insulated, 24 mm, 22 mm, Yellow

Description of article: Wire end ferrule with plastic collar, yellow




[PDF data sheet](#) [Add to Inquiry List](#)

Type: H25,0/36T SW
Order No.: 9021200000

Version:
Wire end ferrule, insulated, 24 mm, 22 mm, Black

Description of article: Wire-end ferrule



[PDF data sheet](#) [Add to Inquiry List](#)