

# GET FULLY EQUIPPED STORAGE DEALS



26" FOAM INLAYS  
Dimensions 543 x 445 mm

### FOAM FF1A74 - 89 Pieces

- 6700SM - 1/4" SOCKETS HEX  
4-4.5-5-5.5-6-7-8-9-10-11-12-13 MM
- A6800DM - 1/4" DEEP SOCKETS HEX  
7-8-8-10-11-13 MM
- 6956 - 1/4" SPINNER
- 6961 - 1/4" EXTENSION 100 MM
- 6966 - 1/4" EXTENSION
- 7800SM - 1/2" SOCKETS HEX  
10-11-12-13-14-15-16-17-18-19-20-21-24-27-30-32-34 MM
- 7805DM - 1/2" SOCKETS DEEP  
10-13-16-17-18-19-16-21
- 7805SM - 1/2" SPARK PLUG  
16-21 MM
- 8160-1/2 / 8162-1/2 - 1/2" EXTENSION 125 - 250 MM
- 8166-1/2 - 1/2" UNIVERSAL JOINT
- 8156-1/2 - 1/2" BREAKER BAR
- 7106S0080 - 1/2" sq 5/16 HEX BIT HOLDER
- 6973 - 1/4" sq 1/4 HEX BIT HOLDER
- 70S/T45 / 70S/T50 / 70S/T55 - 5/16" KÄRJET
- 2058-BR - BIT RATCHET 1/4"
- 59/S31B - 31 PIECES BIT SET
- 6950SL - RATCHET 1/4" SLIM HEAD
- 8150SL - RATCHET 1/2" SLIM HEAD



26" FOAM INLAYS  
Dimensions 543 x 445 mm

### FOAM FF1A75 - 24 Pieces

- BE-9770 - HEX KEY SET HOLDER
- BE-8030 - ERGO™ SCREWDRIVER 3.5 x 0.6 x 75
- BE-8150 - ERGO™ SCREWDRIVER 5.5 x 1.0 x 100
- BE-8611 - ERGO™ SCREWDRIVER PH1 x 75
- BE-8621 - ERGO™ SCREWDRIVER PH2 x 125
- BE-8811 - ERGO™ SCREWDRIVER PZ1 x 75
- BE-8821 - ERGO™ SCREWDRIVER PZ2 x 100
- 111M - COMBINATION WRENCH  
8-10-12-13-14-15-16-17-19



26" FOAM INLAYS  
Dimensions 543 x 445 mm

### FOAM FF1A76 - 30 Pieces

- 3734S/6 - COTTER PIN PUNCHES SET
- 481-400 - GERMAN DIN-HAMMER
- KB18-01 - 18 MM SNAP-OFF BLADE KNIFE TPR
- KSBG18-10DISPEN - 18 MM SNAP-OFF BLADE 10 kpl
- 317-3906 - HACKSAW FRAME
- 3906-300-24-10P - HAND HACKSAW BLADES 10 kpl



## General Maintenance

### 1470K5BKFF1SD

#### 143 piece tool trolley

- 26" 5 drawer Tool Trolley
- Heavy duty construction protects the drawers even if the body is damaged
- Swivel wheels for enhanced manoeuvrability
- Latch system prevents drawers opening while the unit is being moved