



E I DUPONT DE NEMOURS & CO INC
 DUPONT POLYMERS, ENGINEERING POLYMERS
 NYLON RESINS PO BOX 80713, CHESTNUT RUN
 PLAZA, WILMINGTON DE 19880

E41938 (M)



Mtl Dsg	Col	Min Thk mm	UL94 Flame Class	Elec	RTI		H W I	H A I	D V T	4 9	C 5 I
					with Imp	w/o Imp					
Polyamide, Type 66 nylon (PA66), designated "Zytel", furnished in the form of pellets.											
132F, 133L, 135F	All	0.71	94V-2	125	65	65	4	0	—	—	—
		1.5	94V-2	125	75	85	3	0	0	—	—
		3.0	94V-2	125	75	85	2	0	0	6	0
		6.0	94V-2	125	75	85	2	0	0	—	—
✓ 101(f2), 101F, 101L, E101L, E101(f1)	All	0.71	94V-2	125	65	65	4	0	—	—	—
		1.5	94V-2	125	75	85	3	0	0	—	—
101(f2), 101F, 101L, E101L, E101(f1)	All	3.0	94V-2	125	75	85	2	0	0	6	0
		6.0	94V-2	125	75	85	2	0	0	—	—
EFE1068	All	0.71	94V-2	125	65	65	4	0	—	—	—
		1.5	94V-2	125	75	85	3	0	0	—	—
		3.0	94V-2	125	75	85	2	0	0	6	0
		6.0	94V-2	125	75	85	2	0	0	—	—
EFE1030	All	0.71	94V-2	125	—	—	4	0	—	—	—
		1.5	94V-2	125	75	85	3	0	0	—	—
		3.0	94V-2	125	75	85	2	0	0	6	0
		6.0	94V-2	125	75	85	2	0	0	—	—
FE-3370	NC, GY	0.84	94HB	65	65	65	—	—	—	—	—
FE-3397	NC, GY	0.85	94HB	65	65	65	—	—	—	—	—

300 8939

TOLERANCE: L ≤ 10 ±0.2 10 < L ≤ 30 ±0.3 30 < L ≤ 50 ±0.5 50 < L ≤ 100 ±0.7 100 < L ≤ 250 ±1.2 ABOVE 250 ±1.5	APPROVED BY 張道陽 87.5.08.	 品固企業有限公司 品基電子塑膠製品廠 PINGOOD ENTERPRISE CO., LTD.	PART NAME: LED 套 LED HOLDER	REV. A 1
	REVIEWED BY 蕭存桂 87.5.08.			
	DRAWN BY 蕭存桂 87.5.08.			
	MATERIAL: NYLON 66(UL) FLAME CLASS: 94V-2 COLOR: BLACK			
 UNIT mm SCALE 8:1	SHEET 1 OF 1		EFO404505	