

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0451340203](#)  
**Status:** **Active**  
**Overview:** Ultra-Fit Power Connectors  
**Description:** Ultra-Fit™ to Ultra-Fit™ Off-the-Shelf (OTS) Cable Assembly, Single Row, 300.00mm Length, 2 Circuits, White

**Documents:**

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)  
[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	<a href="#">45134</a>
Application	Power, Wire-to-Board
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Ultra-Fit-to-Ultra-Fit
Overview	<a href="#">Ultra-Fit Power Connectors</a>
Product Literature Order No	987651-6143
Product Name	Ultra-Fit OTS
UPC	889056737616

**Physical**

Cable Length	300.00mm
Circuits (Loaded)	2
Color - Resin	White
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	High Conductivity Copper
Material - Plating Mating	Tin over Nickel
Material - Plating Termination	Tin over Nickel
Material - Resin	Nylon
Net Weight	11.726/g
Packaging Type	Bag
Pitch - Mating Interface	3.50mm
Plating min - Mating	1.524µm
Plating min - Termination	1.524µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.35mm
Wire Size AWG	16
Wire/Cable Type	UL 1061

**Electrical**

Current - Maximum per Contact	14.0A
Voltage - Maximum	300V

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	2012341006-000
---------------	----------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant\***

**REACH SVHC**

Not Contained Per -  
ED/30/2017 (7 July  
2017)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

CUST_NOTE	*Product contains part(s) with customer managed
CUST_NOTE1	EHS data. These part(s) are excluded from product compliance status evaluation.
CUST_NOTE2	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

**Search Parts in this Series**

[45134](#) Series

**Mates With**

Ultra-Fit™ Right Angle Header [172310](#)  
<br>Ultra-Fit™ Vertical Header [172286](#) ,  
[172287](#)