

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0151320701**
Status: **Active**
Overview: Pico-Lock Connector System
Description: Pico-Lock-to-Pico-Lock Off-the-Shelf (OTS) Cable Assembly, 1.50mm Pitch, Single Row, 100.00mm Length, 7 Circuits, Black

Documents:

[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|-----------------------------|-----------------------------------|
| Product Family | Cable Assemblies |
| Series | <u>15132</u> |
| Assembly Configuration | Dual Ended Connectors |
| Connector to Connector | Pico-Lock-to-Pico-Lock |
| Overview | <u>Pico-Lock Connector System</u> |
| Product Literature Order No | 987651-6143 |
| Product Name | Pico-Lock OTS |
| UPC | 191128285100 |

Physical

| | |
|--------------------------------|--------------------------------|
| Cable Length | 100.00mm |
| Circuits (Loaded) | 7 |
| Color - Resin | Black |
| Gender | Female-Female |
| Lock to Mating Part | Yes |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Gold |
| Material - Plating Termination | Tin |
| Material - Resin | High Temperature Thermoplastic |
| Net Weight | 2.807/g |
| Pitch - Mating Interface | 1.50mm |
| Single Ended | No |
| Termination Interface: Style | Crimp or Compression |
| Wire Insulation Diameter | 1.10mm |
| Wire Size AWG | 24 |
| Wire/Cable Type | UL 1061 |


Electrical

| | |
|-------------------|------|
| Voltage - Maximum | 150V |
|-------------------|------|

Material Info

Reference - Drawing Numbers

| | |
|---------------|---------------|
| Sales Drawing | 151320700-000 |
|---------------|---------------|



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Not Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

| | |
|-----------------|---------------|
| China ROHS | Green Image |
| ELV | Not Relevant |
| RoHS Phthalates | Not Contained |

Search Parts in this Series

15132 Series

Mates With

504050 Pico-Lock SMT Wire-to-Board
Header