


Produktname | *Product name*: M250F
 Artikelnummer | *Part Number*: 1600-0171
 Anfragenummer | *Inquiry Number*: AN201617
 Ersteller / Datum | *Creator / Date*: LHE / 2017-02-13

Version	Change	Date	Name
V0	---	2017-02-13	LHE

Template name: Light (Non-Rechargeable), Template version: V5

Leuchte / light



Allowable deviation / general tolerances DIN ISO 2768-c

Technische Daten der Leuchte / technical data of the light:



Haupt-LED-Leuchtmittel:	5W LED (Fokussierbar)	Main LED illuminant:	5W LED (Focus able)
Schalterfunktion:	1. schalten: 100%	Switch function:	1. switch: 100%
	2. tippen: 30%		2. tap: 30%
	3. tippen: Strobe		3. tap: strobe
	4. schalten: Aus		4. switch: Off
	5. Morse (tippen)		5. morse (tap)

Lichtstrom: [Lumen] 100% 30%	260lm 75lm	Luminous flux (light output): [Lumen] 100% 30%	260lm 75lm
Leuchtdauer: 100% 30%	ca. 3h 00min ca. 10h 00min	Run time: 100% 30%	approx. 3h 00min approx. 10h 00min
Leuchtweite: 100% 30%	150m 100m	Beam distance: 100% 30%	150m 100m
Maximale Beleuchtungsstärke: [Lux] 100% 30%	5700lx (Abstand:1m) 2500lx (Abstand:1m)	Peak beam illuminance: [Lux] 100% 30%	5700lx (Distance: 1m) 2500lx (Distance: 1m)
Risikogruppe (EN 62471; Bewertet nach DIN IEC/TR 62778 Anhang C.2)	2	Risk group (EN 62471; Assessed with TR 62778 Annex C.2)	2

Benötigte Zellen:	3 x AAA Micro 1.5V Batterien (Alkaline; LR03/AM4/MN2400)	Battery:	3 x AAA Micro 1.5V batteries (Alkaline; LR03/AM4/MN2400)
Schutzart des Gehäuses:	IP54	Degree of protection by the enclosure:	IP54
Gehäusematerial:	Aluminium	Housing material:	Aluminium
Betriebstemperatur:	-10°C...25°C	Operating temperature:	-10°C...25°C
Lagertemperatur:	-10°C...50°C (Nur Alkaline Batterien) -20°C...70°C (Nur Lampe)	Storage temperature:	-10°C...50°C (Alkaline batteries only) -20°C...70°C (Torch only)
Empfohlene Lagerbedingungen: (Nur Alkaline Batterie/Batterien)	Temperatur: 5..25°C Luftfeuchtigkeit: 45..75%	Recommended storage conditions: (Alkaline battery/batteries only)	Temperature: 5...25°C Rel. humidity: 45...75 %
Approbationen:	CE	Approvals:	CE
Gewicht:	126g nur die Lampe 157g mit 3 x Batterien (wie oben beschrieben)	Weight:	126g only the torch 157g with 3 x batteries (as described above)
Lieferumfang:	- 3 x Batterien (wie oben beschrieben)	Shipment:	- 3 x batteries (as described above)

	<ul style="list-style-type: none">- Tragegurt- Gürtelclip- Batteriekartusche		<ul style="list-style-type: none">- <i>Lanyard</i>- <i>Belt clip</i>- <i>Battery cartridge</i>
Verpackung:	Blister-Verpackung	Package:	<i>Blister shell</i>