

# TRACK GAME.

# BY REFUSING TO FOLLOW OUTDATED HUNTING METHODS.

## CompactXR™

LONG-RANGE THERMAL CAMERA DESIGNED FOR YOUR SMARTPHONE

Highly-portable thermal imager, with a narrow 20-degree field of view and detection range up to 1,800 feet, provides hunters a distinct advantage when out in the wild.

Available for iPhone® and Android™



206 x 156  
Thermal  
Sensor



20°  
Field of  
View



-40° F to 626° F  
Detection  
Range



1,800 ft  
Distance



Works  
Day & Night



Waterproof  
Carrying Case



seek™  
thermal

thermal.com

Distributed by:  
Thomas Jacks Limited, Apex House, Timothy's Bridge Road, Statford-upon-Avon, Warwickshire, CV37 9BF  
t 01789 264100 f 01789 264200 e info@thomasjacks.co.uk www.thomasjacks.co.uk

**THOMAS  
JACKS**






SCOUT



TRACK



RECOVER

## CONNECT AND DETECT

- Connect and detect from 1,800 feet for tracking day or night
- 206 x 156 Thermal Sensor for accurate prey spotting
- Never needs charging, so it's always ready to use with your phone
- Portable and lightweight

## LONG-RANGE DETECTION THAT'S EASY TO USE

- Intuitive, free app from Google Play and iTunes AppStore
- Library of color palettes to maximize all thermal imagery
- Customizable performance settings to fully personalize the user experience
- Comes with its own waterproof case to withstand the elements

## SEEK A NEW ADVANTAGE

- Fast startup so that you won't miss an opportunity
- Accurately scout terrain from afar
- Track and recover day or night
- Stay safe without giving position away

## SPECIFICATIONS

DETECTOR & OPTICS	DESCRIPTION
Thermal Sensor	206 x 156
Detection Distance	1,800 feet (600 yards, 550 meters)
Field of View	20 Degree FOV
Temperature Range	-40F to 626F (-40C to 330C)
Frame Rate	< 9 Hz
Focus	Adjustable Focus
Lens Material	Chalcogenide
Microbolometer	Vanadium Oxide
Pixel Pitch	12 Microns
Spectral Range	7.5 - 14 Microns
SYSTEM SPECS	
User Interface	Connects to a smartphone. Controlled by free Seek mobile app.
Temp. Display Scale	Fahrenheit or Celsius
Color Palettes	9 Options
Thermal Tools	Spot Thermography, Hi-Low, and Threshold modes
Capture Settings	Records photos and video
Storage Media	Stores photos and video directly to smartphone
Sharing	Share directly from mobile app to email, text, and social media
Battery	No batteries required. Powered by smartphone
Phone Compatibility	iPhone® and Android™ For compatible phone list, visit <a href="http://thermal.com/supported">thermal.com/supported</a>
DEVICE & PACKAGE INFO	
Country of Origin	Designed and manufactured in Santa Barbara, California, USA with global components
Color	Black
Device Dimensions (H x W x D)	1 x 1.75 x 1 inches
Device Weight	.5 ounces
Box Dimensions (H x W x D)	7 x 3.75 x 1.25 inches
Package Weight	8.3 ounces
Included in the box	Seek CompactXR and Waterproof Carrying Case

For support and user guides visit [support.thermal.com](http://support.thermal.com)



**CompactXR™**  
Available for iPhone® and Android™

**Seek™**  
thermal

[thermal.com](http://thermal.com)

Distributed by:  
Thomas Jacks Limited, Apex House, Timothy's Bridge Road, Statford-upon-Avon, Warwickshire, CV37 9BF  
t 01789 264100 f 01789 264200 e [info@thomasjacks.co.uk](mailto:info@thomasjacks.co.uk) [www.thomasjacks.co.uk](http://www.thomasjacks.co.uk)

