


Solar LED Motion/Light Sensor Security Light



A slim and bright, solar powered LED security light that is both hard wearing and simple to install as it needs no wiring and uses only 2 screws for fitting. Its motion sensor operates at 110° at up to 3m distance and triggers a bright LED light in the hours of darkness, making it ideal for homes, sheds, garages and caravans.

- Solar powered
- Slim robust design
- 110° Motion sensor works up to 3m distance
- Operates at 20% brightness in the hours of darkness until triggered by movement
- Easy to install, uses 2 fixing screws (supplied)
- Ideal for homes, sheds, garages and caravans

In the Box

Solar LED lamp
Fixing bracket
Fixing screws
User manual

Getting started

- Unpack the light and remove all packaging materials.
- Fit the fixing bracket to the wall in a suitable position making sure it provides your property with the maximum coverage angle and is away from any obstructions that could block the sensor path.
- Slot the light into the fixing bracket ensuring its fitted securely.
- To enable the light for the first time, press the mode button to enter stand-by mode.
- In dark conditions (around 10 lux) the light will automatically enter low illumination mode at 20% brightness.
- Once the movement sensor is triggered the lamp will enter high illumination mode at 100% brightness for around 25 seconds, after which the light will return to low illumination mode.
- To turn the light off and on at any time press the mode button. **Please note** turning the light on and off at any time will not affect the solar charging operation.

Technical Specifications

Item code	154.840UK Black , 154.841UK White
Power supply	Solar panel 5.5V 2W
Batteries	2000mAh Li-Ion (not removable)
Luminous flux	370 lumens @ 100% and 40 lumens @ 20%
LED type	36pcs SMD
Colour temperature	6000K
Average lifetime	30,000 hours
IP Rating	IP44
Sensor angle	110°
Sensor distance	Max: 3m
Runtime	4 hours @ 100% and 20 hours @ 20%
Charge time	7 hours
Dimensions	192 x 110 x 30mm
Weight	248g

Safety Disclaimer

- Check the unit for any signs of damage before using for the first time.
- Do not attempt to replace the LED bulbs or service this product yourself as opening or removing covers may result in fire, electric shock or equipment damage and invalidate the warranty.
- Do not expose this product to extreme temperatures or a naked flame.
- Do not look directly into the LED panel or shine in the eyes of others in case of personal injury.
- The LED panel can get hot if on for an extended period, so please do not touch.
- Keep out of the reach of children.



This product is classed as Electrical or Electronic equipment and should not be disposed with other household or commercial waste at the end of its useful life. The goods must be disposed of according to your local council guidelines.