


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1462340100](#)
Status: **Active**
Overview: [Antennas](#)
Description: 698MHz-6GHz Wide Band Antenna, 100.00mm Length

Documents:

3D Model	Packaging Specification 1462340100-PK (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 1462340100-PS (PDF)	Product Literature (PDF)
Application Specification 1462340100-AS (PDF)	



General

Product Family	Antennas
Series	146234
Component Type	Stand Alone Antenna with Cable
Mates With	73412-0110 Microcoaxial RF, 50 Ohm
Overview	Antennas
Product Literature Order No	987651-7811
Product Name	698MHz-6GHz Wide Band Antenna
Protocol	Cellular
Type	Cellular Antenna
UPC	191128461665

Physical

Cable Length	100.00mm
Length	140.00mm
Mounting Style	Adhesive
Net Weight	0.875/g
Packaging Type	PET Film
Polarization	Linear
Radiation Pattern	Omnidirectional
Thickness	0.10mm
Width	20.00mm

Electrical

Band#1 F_End (MHz)	960
Band#1 F_Start (MHz)	698
Band#2 F_End (MHz)	2700
Band#2 F_Start (MHz)	1500
Band#3 F_End (MHz)	6000
Band#3 F_Start (MHz)	2700
Electrical Connectivity	Cable
Impedance	50Ω
Number of Bands	9
Peak Gain (dBi)	1.8 @ 698M, 2.8 @ 1500M, 5.0 @ 2.7G
Return Loss - S11 (dB)	< -4, < -5
Total Efficiency	>70%

Material Info

Reference - Drawing Numbers

Application Specification	1462340100-AS
Packaging Specification	1462340100-PK
Product Specification	1462340100-PS
Sales Drawing	1462340100-SD

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

146234 Series

This document was generated on 01/22/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION