



**QSS-3666H**

**Single Sided Louvered Rack**  
36"L x 12-1/2"W x 66"H

Single sided unit accepts all sizes of Ultra Bins (up to 120 bins) 800 lb. capacity. Shown with QUS240 and QUS250 bins. (Bins sold separately)



**QDS-3666H**

**Double Sided Louvered Rack**  
36"L x 25"W x 66"H

Mobile unit accepts all sizes of Ultra Bins (up to 240 bins) 2,000 lb. capacity. Shown with QUS235 bins. (Bins sold separately)



**QMD-36H**

**Mobile Double Sided Louvered Rack**  
36"L x 25"W x 72"H

Mobile unit accepts all sizes of Ultra Bins (up to 240 bins). Comes complete with four 5" hard rubber, heavy-duty casters, 2 swivel and 2 rigid. 1,200 lb. capacity. Easy to pull handle included. Shown with QUS230 and QUS240 bins. (Bins sold separately)



**QSS-1866H**

**Single Sided Louvered Rack**  
18"L x 12-1/2"W x 66"H

Single sided unit accepts all sizes of Ultra Bins (up to 60 bins) 375 lb. capacity. Shown with QUS245 bins. (Bins sold separately)



**Slanted Shelf**  
see pg. 9

**Flat Shelf**  
see pg. 9

**Wire Mesh Bins**  
see pg. 6

**Plastic Bins**  
see pg. 5

**CUSTOMIZE YOUR OWN UNIT**

1. Select the hanging unit of your choice.
2. Turn to pg. 5 and choose the bin that best fits your need.
3. Go to the chart at the bottom of this page and determine how many bins fit on the unit you selected.
4. Place your order for both unit and bins.

MODEL NO.	DIMENSIONS L" x W" x H"	CTN QTY	CTN WGT
<b>Single Sided Unit, 375 lb. capacity</b>			
QSS-1866H	18"L x 12-1/2"W x 66"H	1	40 lbs
<b>Single Sided Unit, 800 lb. capacity</b>			
QSS-3666H	36"L x 12-1/2"W x 66"H	1	60 lbs
<b>Double Sided Unit, 2,000 lb. capacity</b>			
QDS-3666H	36"L x 25"W x 66"H	1	106 lbs
<b>Double Sided, Mobile Unit, 1,200 lb. capacity</b>			
QMD-36H	36"L x 25"W x 72"H	1	155 lbs

MODEL NO.	QUANTITY OF ULTRA BINS TO FIT LOUVERED RACKS																	
	QUS 200	QUS 210	QUS 220	QUS 221	QUS 224	QUS 230	QUS 234	QUS 235	QUS 239	QUS 240	QUS 241	QUS 242	QUS 245	QUS 250	QUS 255	QUS 260	QUS 265	QUS 270
QSS-1866H	60	60	60	30	30	30	30	15	14	14	14	12	10	7	5	12	5	
QSS-3666H	120	120	120	60	80	60	60	30	28	28	28	24	20	14	21	15	24	10
QDS-3666H	240	240	240	120	160	120	120	60	56	56	48	40	28	42	30	40	40	20
QMD-36H	240	240	240	120	160	120	120	60	56	56	48	40	28	42	30	40	40	20

See pg. 5 for bin dimensions.