


Wiha Protturn Precision Screwdrivers



62990 5 Piece Slotted & Phillips Pocket Pack Set Wiha Protturn precision ball retainer handle & 4 Wiha interchangeable blades.

62990 Set includes the following blades:

↓  **Slotted:** 1.5, 2.0, 3.0, 4.0mm

↓  **Phillips:** #000, #00, #0, #1

↔ **lbs.** .15



95190 6 Pc. Slotted/Phillips Protturn

Precision Screwdriver Set Molded on precision handle. Blade high alloy CVM tool steel, black finish.

Item	Slotted:	↔
No.	2.5x50mm, 3.5x60mm	lbs.

95190	Phillips:	00x40mm, 0x50mm, 1x60mm	.27
-------	-----------	-------------------------	-----



62993 9 Pc. Slotted/Phillips/ TORX® Work Station Set Wiha Protturn precision ball retainer handle & 8 Wiha interchangeable blades.

62993 Set includes the following blades:

↓  **Slotted:** 1.5, 2.0, 3.0, 4.0mm

↓  **Phillips:** #000, #00, #0, #1

↓  **TORX®:** T6, T7, T8, T9, T10, T15, T20

↔ **lbs.** .64



65090 9 Pc. Slotted/Phillips Protturn

Precision Screwdriver Set Molded on precision handle. CVM tool steel, black finish blades.

Item	Slotted:
No.	1.5x40mm, 2.0x5.0mm,

65090	2.5, 3.0, 3.5, 4.0x60mm
-------	-------------------------

	Phillips:	00x40mm, 0x50mm, 1x60mm
--	-----------	-------------------------



96800 Protturn Precision Chip Lifter

Molded on precision handle. Blade CVM tool steel, hardened, black finish.

Item	Size	mm	mm	Inch	lbs.	pkg.
No.	1.0	50	145	5.7	.07	1

96800	1.0	50	145	5.7	.07	1
-------	-----	----	-----	-----	-----	---

Wiha Magnetizer/ Demagnetizer

Magnetize or Demagnetize tools and small parts instantly

Shatterproof Box is made from high quality plastic

Uses 2 C8 industrial permanent magnets



(+) to Magnetize

(-) to Demagnetize

40010 Magnetizer and Demagnetizer

To magnetize and demagnetize steel screwdriver blades, tweezers and similar tools. Box high quality plastic, shock-resistant, green, cadmium free.

Application:

To magnetize, lead tool slowly through the (+) opening, to demagnetize guide tool slowly through the (-) opening.

Item	Dimensions	↔
No.		lbs.

40010	2.1" x 2.0" x 1.1"	.30
-------	--------------------	-----

(Parts under 1" Length or 1/8" Diameter may not demagnetize)



#62995

62995 22 Pc. Slotted/Phillips/ TORX® / Ball End Hex Inch & Metric Tech Pack

Wiha Protturn precision ball retainer handle & 21 interchangeable blades. In canvas storage pouch

62995 Set includes the following blades:

↓  **Slotted:** 1.5, 2.0, 3.0, 4.0mm

↓  **Phillips:** #000, #00, #0, #1

↓  **TORX®:** T6, T7, T8, T9, T10, T15, T20

↓  **Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

↓  **Hex Metric:** 1.5, 2.0, 2.5, 3.0, 4.0mm

↔ **lbs.** .87

62994 14 Pc. Inch/Metric Ball End Hex

Work Tech Pack Protturn precision ball retainer handle & 13 Wiha interchangeable blades.

62994 Set includes the following blades:

↓  **Hex Inch:** .050, 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32"

↓  **Hex Metric:** 1.5, 2.0, 2.5, 3.0, 4.0mm

↔ **lbs.** .66

Set in canvas storage pouch